

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206617

Luminaire Tested: **LD4B10D010 EU4B10209030 4LBWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206617
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10209030 4LBWH1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 766.6 lumens
Efficiency: N/A
Efficacy: 77.4 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206617

CATALOG NUMBER: LD4B10D010 EU4B10209030 4LBWH1

Luminous Intensity Polar Plot





TEST NUMBER: P206617

CATALOG NUMBER: LD4B10D010 EU4B10209030 4LBWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82				82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74				74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67				67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61				61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55				55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50				50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46				46
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43				43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39				39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206617

CATALOG NUMBER: LD4B10D010 EU4B10209030 4LBWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.0	6.1
10°-20°	135.6	17.7
20°-30°	200.1	26.1
30°-40°	197.4	25.8
40°-50°	120.8	15.8
50°-60°	46.3	6.0
60°-70°	14.5	1.9
70°-80°	4.3	0.6
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	382.7	49.9
0°-40°	580.1	75.7
0°-60°	747.3	97.5
0°-90°	766.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	766.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	494	
5°	494	47
15°	481	136
25°	438	200
35°	320	197
45°	155	121
55°	49	46
65°	14	14
75°	4	4
85°	0	1
90°	0	



TEST NUMBER: P206617

CATALOG NUMBER: LD4B10D010 EU4B10209030 4LBWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	494.1
2.5°	495.1
5°	494.1
7.5°	493.0
10°	489.9
12.5°	485.8
15°	480.6
17.5°	474.3
20°	465.0
22.5°	454.6
25°	437.9
27.5°	417.1
30°	391.1
32.5°	358.9
35°	320.4
37.5°	277.7
40°	234.0
42.5°	193.5
45°	155.0
47.5°	120.7
50°	91.5
52.5°	67.6
55°	48.9
57.5°	34.3
60°	25.0
62.5°	18.7
65°	13.5
67.5°	10.4
70°	7.3
72.5°	5.2
75°	4.2
77.5°	2.1
80°	2.1
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)