

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207999

Luminaire Tested: **LD4B30D010 EU4B30509727 4LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207999
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30509727 4LBNMW1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1486.9 lumens
Efficiency: N/A
Efficacy: 53.1 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.95
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207999

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P207999

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	105	103	109	106	104	101	102	100	98	98	97	95	95	94	92	90			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			
3	98	90	84	80	96	89	83	79	86	82	78	84	80	76	81	78	75	73			
4	92	83	76	71	90	82	76	71	80	74	70	78	73	69	76	72	68	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	62	57	53	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	53	49	58	53	49	48			
9	69	58	51	46	68	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	48	43	64	54	47	43	53	47	43	52	47	43	51	46	43	41			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207999

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.7	7.8
10°-20°	305.3	20.5
20°-30°	401.8	27.0
30°-40°	312.8	21.0
40°-50°	151.9	10.2
50°-60°	96.0	6.5
60°-70°	61.9	4.2
70°-80°	32.4	2.2
80°-90°	8.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	823.8	55.4
0°-40°	1136.6	76.4
0°-60°	1384.5	93.1
0°-90°	1486.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1486.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1268	
5°	1245	117
15°	1089	305
25°	886	402
35°	501	313
45°	189	152
55°	106	96
65°	61	62
75°	31	32
85°	7	8
90°	0	



TEST NUMBER: P207999

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1268.4
2.5°	1261.3
5°	1244.8
7.5°	1216.4
10°	1178.6
12.5°	1136.1
15°	1088.9
17.5°	1039.3
20°	987.3
22.5°	937.7
25°	885.7
27.5°	819.6
30°	729.9
32.5°	623.6
35°	500.7
37.5°	387.4
40°	300.0
42.5°	233.8
45°	189.0
47.5°	153.5
50°	134.6
52.5°	120.5
55°	106.3
57.5°	94.5
60°	82.7
62.5°	70.9
65°	61.4
67.5°	54.3
70°	44.9
72.5°	37.8
75°	30.7
77.5°	23.6
80°	16.5
82.5°	11.8
85°	7.1
87.5°	2.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)