

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205586

Luminaire Tested: **LD4B10D010 EU4B10209730 4LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205586
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10209730 4LBSWMH1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 797.8 lumens
Efficiency: N/A
Efficacy: 80.6 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205586

CATALOG NUMBER: LD4B10D010 EU4B10209730 4LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P205586

CATALOG NUMBER: LD4B10D010 EU4B10209730 4LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90																																				
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79																																				
3	96	88	82	76	94	87	81	76	84	79	74	81	77	73	79	75	72	70																																				
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62																																				
5	83	73	65	59	82	72	64	59	70	63	59	68	62	58	66	61	57	56																																				
6	78	66	59	53	76	65	58	53	64	57	53	62	57	52	61	56	52	50																																				
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45																																				
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41																																				
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	49	43	39	38																																				
10	60	48	41	37	59	48	41	37	47	41	36	46	40	36	45	40	36	35																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205586

CATALOG NUMBER: LD4B10D010 EU4B10209730 4LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.7	5.9
10°-20°	123.8	15.5
20°-30°	166.3	20.8
30°-40°	170.3	21.3
40°-50°	147.4	18.5
50°-60°	98.0	12.3
60°-70°	40.2	5.0
70°-80°	4.8	0.6
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	336.9	42.2
0°-40°	507.2	63.6
0°-60°	752.6	94.3
0°-90°	797.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	797.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	506	
5°	498	47
15°	442	124
25°	363	166
35°	272	170
45°	192	147
55°	109	98
65°	40	40
75°	2	5
85°	0	0
90°	0	



TEST NUMBER: P205586

CATALOG NUMBER: LD4B10D010 EU4B10209730 4LBSWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	505.7
2.5°	504.6
5°	497.8
7.5°	487.4
10°	473.2
12.5°	457.6
15°	442.4
17.5°	423.0
20°	404.2
22.5°	384.4
25°	362.9
27.5°	339.9
30°	316.9
32.5°	293.9
35°	271.9
37.5°	251.0
40°	231.1
42.5°	211.3
45°	191.9
47.5°	171.5
50°	150.6
52.5°	129.7
55°	108.8
57.5°	90.5
60°	71.6
62.5°	54.4
65°	39.7
67.5°	26.1
70°	15.2
72.5°	7.3
75°	2.1
77.5°	1.0
80°	0.5
82.5°	0.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)