

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206969

Luminaire Tested: **LD4B30D010 EU4B30509727 4LBWB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206969  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B30D010 EU4B30509727 4LBWB1  
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH SPECULAR BLACK TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1018.8 lumens  
Efficiency: N/A  
Efficacy: 36.4 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206969

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBWB1

### Luminous Intensity Polar Plot





TEST NUMBER: P206969

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBWB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86			86
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79			79
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72			72
5	90	81	75	70	89	80	74	70	79	73	69	77	72	69	75	71	68	67			67
6	85	76	69	65	84	75	69	64	73	68	64	72	67	64	70	66	63	62			62
7	80	71	64	60	79	70	64	59	69	63	59	67	62	59	66	62	58	57			57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	54	62	58	54	53			53
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49			49
10	68	58	52	48	67	58	52	48	57	51	47	56	51	47	55	50	47	46			46

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206969

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBWB1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	80.3	7.9
10°-20°	227.5	22.3
20°-30°	314.5	30.9
30°-40°	269.3	26.4
40°-50°	114.5	11.2
50°-60°	12.8	1.3
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	622.3	61.1
0°-40°	891.6	87.5
0°-60°	1018.8	100.0
0°-90°	1018.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1018.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	850	
5°	846	80
15°	808	228
25°	690	314
35°	437	269
45°	144	114
55°	7	13
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P206969

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBWB1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	850.4
2.5°	848.1
5°	845.7
7.5°	841.0
10°	831.5
12.5°	826.8
15°	807.9
17.5°	791.4
20°	765.4
22.5°	734.7
25°	689.8
27.5°	640.2
30°	583.5
32.5°	515.0
35°	437.0
37.5°	356.7
40°	276.4
42.5°	205.5
45°	144.1
47.5°	89.8
50°	52.0
52.5°	26.0
55°	7.1
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)