

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208101

Luminaire Tested: **LD4B30D010 EU4B30509727 4LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208101
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30509727 4LBWLI1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2063.6 lumens
Efficiency: N/A
Efficacy: 73.7 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208101
CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBWLI1

Luminous Intensity Polar Plot





TEST NUMBER: P208101

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBWLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92																																				
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84																																				
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77																																				
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70																																				
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64																																				
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58																																				
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54																																				
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49																																				
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45																																				
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208101

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBWLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.6	6.0
10°-20°	390.2	18.9
20°-30°	608.7	29.5
30°-40°	592.3	28.7
40°-50°	295.8	14.3
50°-60°	45.8	2.2
60°-70°	5.5	0.3
70°-80°	1.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1122.6	54.4
0°-40°	1714.9	83.1
0°-60°	2056.5	99.7
0°-90°	2063.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2063.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1264	
5°	1281	124
15°	1378	390
25°	1338	609
35°	962	592
45°	371	296
55°	38	46
65°	5	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P208101

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBWLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1264.4
2.5°	1269.1
5°	1281.0
7.5°	1299.9
10°	1323.5
12.5°	1354.2
15°	1377.9
17.5°	1396.8
20°	1399.1
22.5°	1382.6
25°	1337.7
27.5°	1271.5
30°	1188.8
32.5°	1084.8
35°	961.9
37.5°	827.2
40°	685.4
42.5°	534.1
45°	371.1
47.5°	238.7
50°	144.2
52.5°	78.0
55°	37.8
57.5°	16.5
60°	9.5
62.5°	7.1
65°	4.7
67.5°	4.7
70°	2.4
72.5°	2.4
75°	2.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)