

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207072

Luminaire Tested: **LD4B30D010 EU4B30509727 4LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207072
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30509727 4LBWMW1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1820.2 lumens
Efficiency: N/A
Efficacy: 65.0 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207072

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P207072

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78																			
3	96	87	80	75	93	85	79	74	83	77	73	80	76	72	78	74	71	69																			
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61																			
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55																			
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	60	55	51	50																			
7	73	61	53	48	71	60	53	48	59	52	47	57	51	47	56	51	47	45																			
8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41																			
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38																			
10	61	49	42	37	59	48	41	37	47	41	37	46	41	37	46	40	36	35																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207072

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.6	5.7
10°-20°	289.6	15.9
20°-30°	409.3	22.5
30°-40°	396.4	21.8
40°-50°	267.5	14.7
50°-60°	166.0	9.1
60°-70°	111.0	6.1
70°-80°	60.7	3.3
80°-90°	16.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	802.4	44.1
0°-40°	1198.9	65.9
0°-60°	1632.4	89.7
0°-90°	1820.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1820.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1103	
5°	1094	104
15°	1027	290
25°	898	409
35°	638	396
45°	342	268
55°	182	166
65°	111	111
75°	57	61
85°	14	16
90°	0	



TEST NUMBER: P207072

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1103.0
2.5°	1103.0
5°	1093.5
7.5°	1081.7
10°	1067.5
12.5°	1053.4
15°	1027.4
17.5°	1006.1
20°	970.7
22.5°	935.3
25°	897.5
27.5°	845.5
30°	788.8
32.5°	715.6
35°	637.7
37.5°	559.7
40°	481.8
42.5°	403.9
45°	342.5
47.5°	285.8
50°	243.3
52.5°	207.8
55°	181.9
57.5°	160.6
60°	144.1
62.5°	127.5
65°	111.0
67.5°	96.8
70°	82.7
72.5°	70.9
75°	56.7
77.5°	44.9
80°	33.1
82.5°	23.6
85°	14.2
87.5°	4.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)