

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205997

Luminaire Tested: **LD4B10D010 EU4B10209035 4LBSB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205997  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B10D010 EU4B10209035 4LBSB1  
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM  
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W  
DL3-11.1W DLE-11.39W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 803.4 lumens  
Efficiency: N/A  
Efficacy: 81.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205997

CATALOG NUMBER: LD4B10D010 EU4B10209035 4LBSB1

### Luminous Intensity Polar Plot





TEST NUMBER: P205997

CATALOG NUMBER: LD4B10D010 EU4B10209035 4LBSB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88			88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76			76
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65			65
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57			57
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50			50
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44			44
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39			39
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35			35
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32			32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29			29

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205997

CATALOG NUMBER: LD4B10D010 EU4B10209035 4LBSB1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	33.5	4.2
10°-20°	94.9	11.8
20°-30°	141.2	17.6
30°-40°	164.3	20.4
40°-50°	160.2	19.9
50°-60°	123.2	15.3
60°-70°	68.1	8.5
70°-80°	18.0	2.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	269.6	33.6
0°-40°	433.9	54.0
0°-60°	717.2	89.3
0°-90°	803.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	803.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	354	
5°	352	33
15°	336	95
25°	306	141
35°	264	164
45°	208	160
55°	138	123
65°	68	68
75°	15	18
85°	0	0
90°	0	



TEST NUMBER: P205997

CATALOG NUMBER: LD4B10D010 EU4B10209035 4LBSB1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	354.4
2.5°	354.4
5°	352.4
7.5°	349.3
10°	347.3
12.5°	341.2
15°	336.1
17.5°	331.0
20°	323.9
22.5°	316.7
25°	306.5
27.5°	296.4
30°	286.2
32.5°	275.0
35°	263.8
37.5°	249.5
40°	237.3
42.5°	224.1
45°	207.8
47.5°	192.5
50°	175.2
52.5°	156.8
55°	137.5
57.5°	119.2
60°	101.8
62.5°	84.5
65°	68.2
67.5°	53.0
70°	38.7
72.5°	26.5
75°	15.3
77.5°	7.1
80°	1.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)