

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P252090

Luminaire Tested: **LD4B30D010 EU4B30508030 4LBBA1MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P252090
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-4)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30508030 4LBBA1MB
Description: PORTFOLIO 4 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE BLACK TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1458.9 lumens
Efficiency: N/A
Efficacy: 52.1 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 0.94
Luminous Opening: Circular (Dia: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P252090

CATALOG NUMBER: LD4B30D010 EU4B30508030 4LBBA1MB

Luminous Intensity Polar Plot





TEST NUMBER: P252090

CATALOG NUMBER: LD4B30D010 EU4B30508030 4LBBA1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93		
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87		
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81		
4	97	90	84	80	95	88	83	79	86	82	78	84	81	77	82	79	77	75		
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70		
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65		
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61		
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	61	58	57		
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53		
10	72	62	56	52	71	61	56	52	60	55	52	60	55	52	59	55	51	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	142211
5°	141815
10°	140436
15°	138187
20°	134142
25°	123932
30°	100539
35°	62319
40°	29325
45°	10241
50°	2881
55°	1937
60°	1481
65°	1314
70°	1083
75°	715
80°	1066
85°	0



TEST NUMBER: P252090

CATALOG NUMBER: LD4B30D010 EU4B30508030 4LBBA1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.4	9.4
10°-20°	385.0	26.4
20°-30°	517.5	35.5
30°-40°	330.6	22.7
40°-50°	70.3	4.8
50°-60°	10.6	0.7
60°-70°	5.2	0.4
70°-80°	2.3	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1039.8	71.3
0°-40°	1370.4	93.9
0°-60°	1451.3	99.5
0°-90°	1458.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1458.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1459	
5°	1450	137
15°	1370	385
25°	1152	517
35°	524	331
45°	74	70
55°	11	11
65°	6	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P252090

CATALOG NUMBER: LD4B30D010 EU4B30508030 4LBBA1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	1459.2
2.5°	1457.2
5°	1449.6
7.5°	1436.3
10°	1419.1
12.5°	1396.3
15°	1369.6
17.5°	1335.3
20°	1293.4
22.5°	1234.4
25°	1152.5
27.5°	1038.2
30°	893.4
32.5°	714.3
35°	523.8
37.5°	358.1
40°	230.5
42.5°	137.2
45°	74.3
47.5°	38.1
50°	19.0
52.5°	13.3
55°	11.4
57.5°	9.5
60°	7.6
62.5°	5.7
65°	5.7
67.5°	3.8
70°	3.8
72.5°	1.9
75°	1.9
77.5°	1.9
80°	1.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)