

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206237

Luminaire Tested: **LD4B30D010 EU4B30508030 4LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206237
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30508030 4LBPSMW1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3111.4 lumens
Efficiency: N/A
Efficacy: 111.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206237

CATALOG NUMBER: LD4B30D010 EU4B30508030 4LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P206237

CATALOG NUMBER: LD4B30D010 EU4B30508030 4LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206237

CATALOG NUMBER: LD4B30D010 EU4B30508030 4LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.8	3.8
10°-20°	338.6	10.9
20°-30°	509.9	16.4
30°-40°	606.7	19.5
40°-50°	605.6	19.5
50°-60°	492.5	15.8
60°-70°	303.0	9.7
70°-80°	117.4	3.8
80°-90°	18.8	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	967.3	31.1
0°-40°	1574.0	50.6
0°-60°	2672.2	85.9
0°-90°	3111.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3111.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1254	
5°	1250	119
15°	1202	339
25°	1110	510
35°	972	607
45°	787	606
55°	551	493
65°	304	303
75°	107	117
85°	15	19
90°	0	



TEST NUMBER: P206237

CATALOG NUMBER: LD4B30D010 EU4B30508030 4LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1253.6
2.5°	1255.4
5°	1249.9
7.5°	1242.5
10°	1233.3
12.5°	1216.7
15°	1202.0
17.5°	1179.8
20°	1155.9
22.5°	1133.8
25°	1109.8
27.5°	1076.6
30°	1043.4
32.5°	1012.1
35°	971.5
37.5°	927.3
40°	886.7
42.5°	837.0
45°	787.2
47.5°	733.7
50°	676.6
52.5°	617.6
55°	551.2
57.5°	486.7
60°	424.0
62.5°	363.2
65°	304.2
67.5°	248.9
70°	197.3
72.5°	149.3
75°	106.9
77.5°	70.1
80°	42.4
82.5°	25.8
85°	14.7
87.5°	7.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)