

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P251981

Luminaire Tested: **LD4B10D010 EU4B10209040 4LBBA1MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P251981  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-3)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B10D010 EU4B10209040 4LBBA1MW  
Description: PORTFOLIO 4 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1115.0 lumens  
Efficiency: N/A  
Efficacy: 110.9 lumens/watt  
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.99  
Luminous Opening: Circular (Dia: 0.38' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 10.05  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251981

CATALOG NUMBER: LD4B10D010 EU4B10209040 4LBBA1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P251981

CATALOG NUMBER: LD4B10D010 EU4B10209040 4LBBA1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78			
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69			
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56			
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51			
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	58	50	45	68	57	50	45	56	49	45	54	49	45	53	48	44	43			
9	65	54	46	42	64	53	46	42	52	46	41	51	45	41	50	45	41	39			
10	62	50	43	39	61	50	43	38	49	43	38	48	42	38	47	42	38	37			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	75998
5°	75212
10°	72954
15°	70032
20°	66874
25°	62541
30°	54444
35°	42010
40°	31080
45°	24464
50°	21014
55°	19098
60°	17406
65°	16119
70°	14903
75°	13970
80°	12965
85°	12188



TEST NUMBER: P251981

CATALOG NUMBER: LD4B10D010 EU4B10209040 4LBBA1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.4	6.5
10°-20°	195.1	17.5
20°-30°	263.9	23.7
30°-40°	221.8	19.9
40°-50°	140.3	12.6
50°-60°	100.8	9.0
60°-70°	69.4	6.2
70°-80°	39.3	3.5
80°-90°	12.1	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	531.4	47.7
0°-40°	753.2	67.5
0°-60°	994.3	89.2
0°-90°	1115.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1115.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	780	
5°	769	72
15°	694	195
25°	582	264
35°	353	222
45°	178	140
55°	112	101
65°	70	69
75°	37	39
85°	11	12
90°	0	



TEST NUMBER: P251981

CATALOG NUMBER: LD4B10D010 EU4B10209040 4LBBA1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	779.8
2.5°	777.3
5°	768.8
7.5°	754.9
10°	737.2
12.5°	716.6
15°	694.1
17.5°	669.8
20°	644.8
22.5°	615.7
25°	581.6
27.5°	537.9
30°	483.8
32.5°	420.6
35°	353.1
37.5°	293.6
40°	244.3
42.5°	206.0
45°	177.5
47.5°	155.6
50°	138.6
52.5°	124.6
55°	112.4
57.5°	100.3
60°	89.3
62.5°	79.0
65°	69.9
67.5°	60.8
70°	52.3
72.5°	44.4
75°	37.1
77.5°	29.8
80°	23.1
82.5°	17.0
85°	10.9
87.5°	4.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)