

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206347

Luminaire Tested: **LD4B30D010 EU4B30509030 4LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206347
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30509030 4LBCSMW1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2600.5 lumens
Efficiency: N/A
Efficacy: 92.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206347

CATALOG NUMBER: LD4B30D010 EU4B30509030 4LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P206347

CATALOG NUMBER: LD4B30D010 EU4B30509030 4LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206347

CATALOG NUMBER: LD4B30D010 EU4B30509030 4LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.6	3.9
10°-20°	286.5	11.0
20°-30°	431.0	16.6
30°-40°	510.8	19.6
40°-50°	508.3	19.5
50°-60°	409.7	15.8
60°-70°	247.9	9.5
70°-80°	92.0	3.5
80°-90°	13.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	818.1	31.5
0°-40°	1328.9	51.1
0°-60°	2246.9	86.4
0°-90°	2600.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2600.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1062	
5°	1057	101
15°	1015	286
25°	936	431
35°	818	511
45°	662	508
55°	457	410
65°	249	248
75°	84	92
85°	11	14
90°	0	



TEST NUMBER: P206347

CATALOG NUMBER: LD4B30D010 EU4B30509030 4LBCSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1062.1
2.5°	1062.1
5°	1057.4
7.5°	1054.2
10°	1044.8
12.5°	1029.0
15°	1014.8
17.5°	999.1
20°	980.2
22.5°	961.3
25°	936.1
27.5°	909.3
30°	879.3
32.5°	851.0
35°	817.9
37.5°	783.2
40°	742.2
42.5°	702.8
45°	661.9
47.5°	616.2
50°	565.7
52.5°	513.7
55°	457.0
57.5°	406.6
60°	349.8
62.5°	299.4
65°	249.0
67.5°	201.7
70°	157.6
72.5°	118.2
75°	83.5
77.5°	53.6
80°	31.5
82.5°	18.9
85°	11.0
87.5°	4.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)