

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207031

Luminaire Tested: **LD4B10D010 EU4B10209040 4LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207031
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10209040 4LBWMW1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 813.5 lumens
Efficiency: N/A
Efficacy: 82.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207031

CATALOG NUMBER: LD4B10D010 EU4B10209040 4LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P207031

CATALOG NUMBER: LD4B10D010 EU4B10209040 4LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78			
3	96	87	80	75	93	85	79	74	83	77	73	80	76	72	78	74	71	69			
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61			
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55			
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	60	55	51	50			
7	73	61	53	48	71	60	53	48	59	52	47	57	51	47	56	51	47	45			
8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41			
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38			
10	61	49	42	37	59	48	41	37	47	41	37	46	41	37	46	40	36	35			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207031

CATALOG NUMBER: LD4B10D010 EU4B10209040 4LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.3	5.7
10°-20°	129.4	15.9
20°-30°	182.9	22.5
30°-40°	177.2	21.8
40°-50°	119.6	14.7
50°-60°	74.2	9.1
60°-70°	49.6	6.1
70°-80°	27.1	3.3
80°-90°	7.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	358.6	44.1
0°-40°	535.8	65.9
0°-60°	729.6	89.7
0°-90°	813.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	813.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	493	
5°	489	46
15°	459	129
25°	401	183
35°	285	177
45°	153	120
55°	81	74
65°	50	50
75°	25	27
85°	6	7
90°	0	



TEST NUMBER: P207031

CATALOG NUMBER: LD4B10D010 EU4B10209040 4LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	493.0
2.5°	493.0
5°	488.8
7.5°	483.5
10°	477.1
12.5°	470.8
15°	459.2
17.5°	449.7
20°	433.9
22.5°	418.0
25°	401.1
27.5°	377.9
30°	352.6
32.5°	319.9
35°	285.0
37.5°	250.2
40°	215.3
42.5°	180.5
45°	153.1
47.5°	127.7
50°	108.7
52.5°	92.9
55°	81.3
57.5°	71.8
60°	64.4
62.5°	57.0
65°	49.6
67.5°	43.3
70°	36.9
72.5°	31.7
75°	25.3
77.5°	20.1
80°	14.8
82.5°	10.6
85°	6.3
87.5°	2.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)