

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208097

Luminaire Tested: **LD4B30D010 EU4B30509030 4LBWLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P208097  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B30D010 EU4B30509030 4LBWLI1  
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2467.7 lumens  
Efficiency: N/A  
Efficacy: 88.1 lumens/watt  
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P208097

CATALOG NUMBER: LD4B30D010 EU4B30509030 4LBWLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P208097

CATALOG NUMBER: LD4B30D010 EU4B30509030 4LBWLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			92																
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			84																
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77			77																
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70			70																
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64			64																
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58			58																
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54			54																
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49			49																
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45			45																
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42			42																

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P208097

CATALOG NUMBER: LD4B30D010 EU4B30509030 4LBWL11

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	147.9	6.0
10°-20°	466.6	18.9
20°-30°	727.9	29.5
30°-40°	708.3	28.7
40°-50°	353.8	14.3
50°-60°	54.8	2.2
60°-70°	6.6	0.3
70°-80°	1.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1342.4	54.4
0°-40°	2050.7	83.1
0°-60°	2459.2	99.7
0°-90°	2467.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2467.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1512	
5°	1532	148
15°	1648	467
25°	1600	728
35°	1150	708
45°	444	354
55°	45	55
65°	6	7
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P208097

CATALOG NUMBER: LD4B30D010 EU4B30509030 4LBWLI1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1512.0
2.5°	1517.7
5°	1531.8
7.5°	1554.4
10°	1582.7
12.5°	1619.4
15°	1647.7
17.5°	1670.3
20°	1673.1
22.5°	1653.3
25°	1599.6
27.5°	1520.5
30°	1421.6
32.5°	1297.2
35°	1150.3
37.5°	989.2
40°	819.6
42.5°	638.7
45°	443.7
47.5°	285.4
50°	172.4
52.5°	93.3
55°	45.2
57.5°	19.8
60°	11.3
62.5°	8.5
65°	5.7
67.5°	5.7
70°	2.8
72.5°	2.8
75°	2.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)