

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206759

Luminaire Tested: **LD4B30D010 EU4B30509030 4LBWWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206759  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B30D010 EU4B30509030 4LBWWH1  
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2162.5 lumens  
Efficiency: N/A  
Efficacy: 77.2 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206759

CATALOG NUMBER: LD4B30D010 EU4B30509030 4LBWWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P206759

CATALOG NUMBER: LD4B30D010 EU4B30509030 4LBWWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92				92															
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	85	84				84															
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76				76															
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69				69															
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63				63															
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58				58															
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53				53															
8	73	62	56	51	72	62	55	51	61	55	51	60	54	50	59	54	50	49				49															
9	69	58	51	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45				45															
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41				41															

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206759

CATALOG NUMBER: LD4B30D010 EU4B30509030 4LBWWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	131.0	6.1
10°-20°	405.3	18.7
20°-30°	623.4	28.8
30°-40°	601.5	27.8
40°-50°	313.6	14.5
50°-60°	66.0	3.1
60°-70°	15.3	0.7
70°-80°	6.0	0.3
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1159.7	53.6
0°-40°	1761.2	81.4
0°-60°	2140.8	99.0
0°-90°	2162.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2162.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1352	
5°	1363	131
15°	1434	405
25°	1366	623
35°	976	602
45°	399	314
55°	59	66
65°	14	15
75°	6	6
85°	0	0
90°	0	



TEST NUMBER: P206759

CATALOG NUMBER: LD4B30D010 EU4B30509030 4LBWWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1352.1
2.5°	1354.9
5°	1363.4
7.5°	1374.7
10°	1391.7
12.5°	1414.3
15°	1434.1
17.5°	1445.4
20°	1436.9
22.5°	1420.0
25°	1366.2
27.5°	1301.2
30°	1216.3
32.5°	1103.2
35°	975.9
37.5°	837.3
40°	693.0
42.5°	548.7
45°	398.8
47.5°	268.7
50°	172.5
52.5°	104.7
55°	59.4
57.5°	36.8
60°	25.5
62.5°	19.8
65°	14.1
67.5°	11.3
70°	8.5
72.5°	8.5
75°	5.7
77.5°	2.8
80°	2.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)