

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207176

Luminaire Tested: **LD4B30D010 EU4B30509730 4LBMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P207176  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B30D010 EU4B30509730 4LBMH1  
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1638.2 lumens  
Efficiency: N/A  
Efficacy: 58.5 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P207176

CATALOG NUMBER: LD4B30D010 EU4B30509730 4LBMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P207176

CATALOG NUMBER: LD4B30D010 EU4B30509730 4LBMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79			
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73			
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67			
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62			
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58			
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54			
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50			
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P207176

CATALOG NUMBER: LD4B30D010 EU4B30509730 4LBMH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	149.5	9.1
10°-20°	392.1	23.9
20°-30°	503.9	30.8
30°-40°	379.1	23.1
40°-50°	152.3	9.3
50°-60°	43.3	2.6
60°-70°	13.7	0.8
70°-80°	3.9	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1045.5	63.8
0°-40°	1424.7	87.0
0°-60°	1620.2	98.9
0°-90°	1638.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1638.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1624	
5°	1595	149
15°	1399	392
25°	1113	504
35°	608	379
45°	188	152
55°	44	43
65°	12	14
75°	2	4
85°	0	0
90°	0	



TEST NUMBER: P207176

CATALOG NUMBER: LD4B30D010 EU4B30509730 4LBMH1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1624.4
2.5°	1614.5
5°	1594.7
7.5°	1557.6
10°	1510.7
12.5°	1453.8
15°	1399.4
17.5°	1337.6
20°	1270.8
22.5°	1199.1
25°	1112.6
27.5°	1008.8
30°	887.6
32.5°	751.6
35°	608.2
37.5°	474.7
40°	356.0
42.5°	262.1
45°	187.9
47.5°	128.6
50°	89.0
52.5°	61.8
55°	44.5
57.5°	32.1
60°	24.7
62.5°	17.3
65°	12.4
67.5°	9.9
70°	7.4
72.5°	4.9
75°	2.5
77.5°	2.5
80°	2.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)