

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207542

Luminaire Tested: **LD4B10D010 EU4B10208050 4LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207542
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10208050 4LBMMW1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 870.5 lumens
Efficiency: N/A
Efficacy: 87.9 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207542

CATALOG NUMBER: LD4B10D010 EU4B10208050 4LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P207542

CATALOG NUMBER: LD4B10D010 EU4B10208050 4LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89	89	89	89
2	104	98	92	88	102	96	91	87	93	89	85	89	86	83	87	84	81	80	80	80	80
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71	71	71	71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	69	66	64	64	64	64
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58	58	58	58
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53	53	53	53
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49	49	49	49
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45	45	45	45
9	67	55	48	44	66	55	48	44	54	48	44	53	47	43	52	47	43	42	42	42	42
10	63	52	45	41	62	51	45	41	51	45	40	50	44	40	49	44	40	39	39	39	39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207542

CATALOG NUMBER: LD4B10D010 EU4B10208050 4LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.3	7.0
10°-20°	164.2	18.9
20°-30°	218.3	25.1
30°-40°	178.6	20.5
40°-50°	104.0	11.9
50°-60°	69.0	7.9
60°-70°	45.4	5.2
70°-80°	23.9	2.7
80°-90°	5.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	443.8	51.0
0°-40°	622.4	71.5
0°-60°	795.4	91.4
0°-90°	870.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	870.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	661	
5°	653	61
15°	585	164
25°	479	218
35°	285	179
45°	131	104
55°	77	69
65°	45	45
75°	23	24
85°	5	6
90°	0	



TEST NUMBER: P207542

CATALOG NUMBER: LD4B10D010 EU4B10208050 4LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	660.8
2.5°	659.6
5°	653.3
7.5°	638.1
10°	621.7
12.5°	606.6
15°	585.2
17.5°	561.2
20°	541.0
22.5°	513.3
25°	479.2
27.5°	442.7
30°	396.0
32.5°	340.5
35°	285.0
37.5°	234.6
40°	190.4
42.5°	156.4
45°	131.2
47.5°	111.0
50°	97.1
52.5°	85.8
55°	76.9
57.5°	68.1
60°	59.3
62.5°	53.0
65°	45.4
67.5°	39.1
70°	32.8
72.5°	27.7
75°	22.7
77.5°	17.7
80°	12.6
82.5°	8.8
85°	5.0
87.5°	1.3
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)