

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206144

Luminaire Tested: **LD4B30D010 EU4B30509730 4LBSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206144
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30509730 4LBSMW1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3125.2 lumens
Efficiency: N/A
Efficacy: 111.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206144

CATALOG NUMBER: LD4B30D010 EU4B30509730 4LBSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P206144

CATALOG NUMBER: LD4B30D010 EU4B30509730 4LBSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206144

CATALOG NUMBER: LD4B30D010 EU4B30509730 4LBSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.3	3.8
10°-20°	340.1	10.9
20°-30°	512.2	16.4
30°-40°	609.4	19.5
40°-50°	608.3	19.5
50°-60°	494.7	15.8
60°-70°	304.4	9.7
70°-80°	117.9	3.8
80°-90°	18.9	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	971.6	31.1
0°-40°	1581.0	50.6
0°-60°	2684.1	85.9
0°-90°	3125.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3125.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1259	
5°	1256	119
15°	1207	340
25°	1115	512
35°	976	609
45°	791	608
55°	554	495
65°	306	304
75°	107	118
85°	15	19
90°	0	



TEST NUMBER: P206144

CATALOG NUMBER: LD4B30D010 EU4B30509730 4LBSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1259.2
2.5°	1261.0
5°	1255.5
7.5°	1248.0
10°	1238.8
12.5°	1222.1
15°	1207.3
17.5°	1185.1
20°	1161.0
22.5°	1138.8
25°	1114.7
27.5°	1081.4
30°	1048.1
32.5°	1016.6
35°	975.8
37.5°	931.4
40°	890.7
42.5°	840.7
45°	790.7
47.5°	737.0
50°	679.6
52.5°	620.3
55°	553.7
57.5°	488.8
60°	425.9
62.5°	364.8
65°	305.5
67.5°	250.0
70°	198.1
72.5°	150.0
75°	107.4
77.5°	70.4
80°	42.6
82.5°	25.9
85°	14.8
87.5°	7.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)