

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206970

Luminaire Tested: **LD4B30D010 EU4B30509730 4LBWB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206970
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30509730 4LBWB1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1064.9 lumens
Efficiency: N/A
Efficacy: 38.0 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206970

CATALOG NUMBER: LD4B30D010 EU4B30509730 4LBWB1

Luminous Intensity Polar Plot





TEST NUMBER: P206970

CATALOG NUMBER: LD4B30D010 EU4B30509730 4LBWB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79			
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72			
5	90	81	75	70	89	80	74	70	79	73	69	77	72	69	75	71	68	67			
6	85	76	69	65	84	75	69	64	73	68	64	72	67	64	70	66	63	62			
7	80	71	64	60	79	70	64	59	69	63	59	67	62	59	66	62	58	57			
8	76	66	60	55	75	65	59	55	64	59	55	63	58	54	62	58	54	53			
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49			
10	68	58	52	48	67	58	52	48	57	51	47	56	51	47	55	50	47	46			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206970

CATALOG NUMBER: LD4B30D010 EU4B30509730 4LBWB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.9	7.9
10°-20°	237.8	22.3
20°-30°	328.7	30.9
30°-40°	281.4	26.4
40°-50°	119.6	11.2
50°-60°	13.4	1.3
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	650.5	61.1
0°-40°	931.9	87.5
0°-60°	1064.9	100.0
0°-90°	1064.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1064.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	889	
5°	884	84
15°	844	238
25°	721	329
35°	457	281
45°	151	120
55°	7	13
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P206970

CATALOG NUMBER: LD4B30D010 EU4B30509730 4LBWB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	889.0
2.5°	886.5
5°	884.0
7.5°	879.1
10°	869.2
12.5°	864.3
15°	844.5
17.5°	827.2
20°	800.1
22.5°	768.0
25°	721.0
27.5°	669.2
30°	609.9
32.5°	538.3
35°	456.8
37.5°	372.9
40°	288.9
42.5°	214.8
45°	150.6
47.5°	93.8
50°	54.3
52.5°	27.2
55°	7.4
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)