

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207784

Luminaire Tested: **LD4B30D010 EU4B30508035 4LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207784
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30508035 4LBNGPH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1400.9 lumens
Efficiency: N/A
Efficacy: 50.0 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.88
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207784

CATALOG NUMBER: LD4B30D010 EU4B30508035 4LBNGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P207784

CATALOG NUMBER: LD4B30D010 EU4B30508035 4LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	68	63	60	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	52	51			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207784

CATALOG NUMBER: LD4B30D010 EU4B30508035 4LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.7	10.9
10°-20°	382.9	27.3
20°-30°	466.6	33.3
30°-40°	307.9	22.0
40°-50°	70.9	5.1
50°-60°	13.6	1.0
60°-70°	5.0	0.4
70°-80°	1.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1002.2	71.5
0°-40°	1310.1	93.5
0°-60°	1394.6	99.5
0°-90°	1400.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1400.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1680	
5°	1639	153
15°	1371	383
25°	1025	467
35°	492	308
45°	78	71
55°	14	14
65°	3	5
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P207784

CATALOG NUMBER: LD4B30D010 EU4B30508035 4LBNGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1679.9
2.5°	1676.5
5°	1639.2
7.5°	1588.3
10°	1520.4
12.5°	1452.5
15°	1371.1
17.5°	1286.2
20°	1198.0
22.5°	1119.9
25°	1024.9
27.5°	929.9
30°	807.7
32.5°	658.4
35°	492.1
37.5°	342.8
40°	220.6
42.5°	135.8
45°	78.1
47.5°	40.7
50°	23.8
52.5°	20.4
55°	13.6
57.5°	10.2
60°	10.2
62.5°	6.8
65°	3.4
67.5°	3.4
70°	3.4
72.5°	3.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)