

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206319

Luminaire Tested: **LD4B15D010 EU4B10209024 4LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206319
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10209024 4LBSCMW1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1127.7 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206319

CATALOG NUMBER: LD4B15D010 EU4B10209024 4LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P206319

CATALOG NUMBER: LD4B15D010 EU4B10209024 4LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206319

CATALOG NUMBER: LD4B15D010 EU4B10209024 4LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.6	3.9
10°-20°	124.2	11.0
20°-30°	186.9	16.6
30°-40°	221.5	19.6
40°-50°	220.4	19.5
50°-60°	177.7	15.8
60°-70°	107.5	9.5
70°-80°	39.9	3.5
80°-90°	6.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	354.7	31.5
0°-40°	576.2	51.1
0°-60°	974.3	86.4
0°-90°	1127.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1127.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	461	
5°	458	44
15°	440	124
25°	406	187
35°	355	221
45°	287	220
55°	198	178
65°	108	107
75°	36	40
85°	5	6
90°	0	



TEST NUMBER: P206319

CATALOG NUMBER: LD4B15D010 EU4B10209024 4LBCSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	460.6
2.5°	460.6
5°	458.5
7.5°	457.2
10°	453.1
12.5°	446.2
15°	440.1
17.5°	433.2
20°	425.0
22.5°	416.8
25°	405.9
27.5°	394.3
30°	381.3
32.5°	369.0
35°	354.7
37.5°	339.6
40°	321.9
42.5°	304.8
45°	287.0
47.5°	267.2
50°	245.3
52.5°	222.8
55°	198.2
57.5°	176.3
60°	151.7
62.5°	129.8
65°	108.0
67.5°	87.5
70°	68.3
72.5°	51.3
75°	36.2
77.5°	23.2
80°	13.7
82.5°	8.2
85°	4.8
87.5°	2.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)