

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207452

Luminaire Tested: **LD4B15D010 EU4B10209024 4LBMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207452
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10209024 4LBMB1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 445.0 lumens
Efficiency: N/A
Efficacy: 31.1 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.87
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207452

CATALOG NUMBER: LD4B15D010 EU4B10209024 4LBMB1

Luminous Intensity Polar Plot





TEST NUMBER: P207452

CATALOG NUMBER: LD4B15D010 EU4B10209024 4LBMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94																			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82																			
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	77																			
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72																			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																			
7	84	75	70	65	83	75	69	65	73	68	65	72	68	65	71	67	64	63																			
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59																			
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56																			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207452

CATALOG NUMBER: LD4B15D010 EU4B10209024 4LBMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.5	11.3
10°-20°	125.5	28.2
20°-30°	151.8	34.1
30°-40°	96.8	21.8
40°-50°	20.2	4.5
50°-60°	0.3	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	327.7	73.6
0°-40°	424.5	95.4
0°-60°	445.0	100.0
0°-90°	445.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	445.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	558	
5°	541	50
15°	448	125
25°	338	152
35°	155	97
45°	21	20
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P207452

CATALOG NUMBER: LD4B15D010 EU4B10209024 4LBMB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	558.5
2.5°	552.4
5°	541.4
7.5°	525.4
10°	502.1
12.5°	473.8
15°	448.1
17.5°	422.3
20°	394.1
22.5°	367.0
25°	337.6
27.5°	298.3
30°	255.3
32.5°	205.0
35°	154.7
37.5°	108.0
40°	71.2
42.5°	41.7
45°	20.9
47.5°	8.6
50°	2.5
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)