

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207579

Luminaire Tested: **LD4B30D010 EU4B30508040 4LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207579
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30508040 4LBMMW1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2365.7 lumens
Efficiency: N/A
Efficacy: 84.5 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207579

CATALOG NUMBER: LD4B30D010 EU4B30508040 4LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P207579

CATALOG NUMBER: LD4B30D010 EU4B30508040 4LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89																			
2	104	98	92	88	102	96	91	87	93	89	85	89	86	83	87	84	81	80																			
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71																			
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	69	66	64																			
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58																			
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53																			
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49																			
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45																			
9	67	55	48	44	66	55	48	44	54	48	44	53	47	43	52	47	43	42																			
10	63	52	45	41	62	51	45	41	51	45	40	50	44	40	49	44	40	39																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207579

CATALOG NUMBER: LD4B30D010 EU4B30508040 4LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.5	7.0
10°-20°	446.2	18.9
20°-30°	593.4	25.1
30°-40°	485.3	20.5
40°-50°	282.7	11.9
50°-60°	187.5	7.9
60°-70°	123.3	5.2
70°-80°	65.1	2.8
80°-90°	15.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1206.1	51.0
0°-40°	1691.4	71.5
0°-60°	2161.5	91.4
0°-90°	2365.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2365.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1796	
5°	1775	166
15°	1590	446
25°	1302	593
35°	775	485
45°	356	283
55°	209	188
65°	123	123
75°	62	65
85°	14	16
90°	0	



TEST NUMBER: P207579

CATALOG NUMBER: LD4B30D010 EU4B30508040 4LBMMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1795.9
2.5°	1792.4
5°	1775.3
7.5°	1734.2
10°	1689.6
12.5°	1648.5
15°	1590.2
17.5°	1525.1
20°	1470.3
22.5°	1394.9
25°	1302.3
27.5°	1203.0
30°	1076.1
32.5°	925.3
35°	774.6
37.5°	637.5
40°	517.5
42.5°	425.0
45°	356.4
47.5°	301.6
50°	263.9
52.5°	233.1
55°	209.1
57.5°	185.1
60°	161.1
62.5°	143.9
65°	123.4
67.5°	106.2
70°	89.1
72.5°	75.4
75°	61.7
77.5°	48.0
80°	34.3
82.5°	24.0
85°	13.7
87.5°	3.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)