

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208093

Luminaire Tested: **LD4B30D010 EU4B30508040 4LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208093
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30508040 4LBWLI1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2993.1 lumens
Efficiency: N/A
Efficacy: 106.9 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208093

CATALOG NUMBER: LD4B30D010 EU4B30508040 4LBWLI1

Luminous Intensity Polar Plot





TEST NUMBER: P208093

CATALOG NUMBER: LD4B30D010 EU4B30508040 4LBWLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54	54	54	54
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208093

CATALOG NUMBER: LD4B30D010 EU4B30508040 4LBWL11

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.3	6.0
10°-20°	566.0	18.9
20°-30°	882.9	29.5
30°-40°	859.1	28.7
40°-50°	429.1	14.3
50°-60°	66.4	2.2
60°-70°	8.0	0.3
70°-80°	2.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1628.2	54.4
0°-40°	2487.3	83.1
0°-60°	2982.8	99.7
0°-90°	2993.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2993.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1834	
5°	1858	179
15°	1998	566
25°	1940	883
35°	1395	859
45°	538	429
55°	55	66
65°	7	8
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P208093

CATALOG NUMBER: LD4B30D010 EU4B30508040 4LBWLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1833.9
2.5°	1840.8
5°	1857.9
7.5°	1885.4
10°	1919.6
12.5°	1964.2
15°	1998.5
17.5°	2025.9
20°	2029.3
22.5°	2005.3
25°	1940.2
27.5°	1844.2
30°	1724.2
32.5°	1573.4
35°	1395.2
37.5°	1199.8
40°	994.1
42.5°	774.7
45°	538.2
47.5°	346.2
50°	209.1
52.5°	113.1
55°	54.8
57.5°	24.0
60°	13.7
62.5°	10.3
65°	6.9
67.5°	6.9
70°	3.4
72.5°	3.4
75°	3.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)