

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207552

Luminaire Tested: **LD4B15D010 EU4B10208035 4LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207552
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10208035 4LBMMW1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1199.5 lumens
Efficiency: N/A
Efficacy: 83.9 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207552

CATALOG NUMBER: LD4B15D010 EU4B10208035 4LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P207552

CATALOG NUMBER: LD4B15D010 EU4B10208035 4LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89	89	89	89
2	104	98	92	88	102	96	91	87	93	89	85	89	86	83	87	84	81	80	80	80	80
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71	71	71	71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	69	66	64	64	64	64
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58	58	58	58
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53	53	53	53
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49	49	49	49
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45	45	45	45
9	67	55	48	44	66	55	48	44	54	48	44	53	47	43	52	47	43	42	42	42	42
10	63	52	45	41	62	51	45	41	51	45	40	50	44	40	49	44	40	39	39	39	39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207552

CATALOG NUMBER: LD4B15D010 EU4B10208035 4LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.4	7.0
10°-20°	226.2	18.9
20°-30°	300.8	25.1
30°-40°	246.1	20.5
40°-50°	143.3	11.9
50°-60°	95.1	7.9
60°-70°	62.5	5.2
70°-80°	33.0	2.7
80°-90°	8.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	611.5	51.0
0°-40°	857.5	71.5
0°-60°	1095.9	91.4
0°-90°	1199.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1199.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	910	
5°	900	84
15°	806	226
25°	660	301
35°	393	246
45°	181	143
55°	106	95
65°	63	63
75°	31	33
85°	7	8
90°	0	



TEST NUMBER: P207552

CATALOG NUMBER: LD4B15D010 EU4B10208035 4LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	910.5
2.5°	908.8
5°	900.1
7.5°	879.2
10°	856.7
12.5°	835.8
15°	806.3
17.5°	773.2
20°	745.4
22.5°	707.2
25°	660.3
27.5°	609.9
30°	545.6
32.5°	469.2
35°	392.7
37.5°	323.2
40°	262.4
42.5°	215.5
45°	180.7
47.5°	152.9
50°	133.8
52.5°	118.2
55°	106.0
57.5°	93.8
60°	81.7
62.5°	73.0
65°	62.6
67.5°	53.9
70°	45.2
72.5°	38.2
75°	31.3
77.5°	24.3
80°	17.4
82.5°	12.2
85°	7.0
87.5°	1.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)