

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208473

Luminaire Tested: **LD4B15D010 EU4B10208035 4LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208473
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10208035 4LBNWH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1006.5 lumens
Efficiency: N/A
Efficacy: 70.4 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.62
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208473

CATALOG NUMBER: LD4B15D010 EU4B10208035 4LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P208473

CATALOG NUMBER: LD4B15D010 EU4B10208035 4LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | |
| 1 | 114 | 111 | 109 | 107 | 112 | 109 | 107 | 105 | 105 | 104 | 102 | 102 | 100 | 99 | 98 | 97 | 96 | 95 | | |
| 2 | 109 | 105 | 101 | 98 | 107 | 103 | 100 | 97 | 100 | 97 | 95 | 97 | 95 | 93 | 94 | 92 | 91 | 89 | | |
| 3 | 104 | 98 | 94 | 90 | 102 | 97 | 93 | 90 | 94 | 91 | 88 | 92 | 89 | 87 | 90 | 87 | 85 | 84 | | |
| 4 | 100 | 93 | 88 | 84 | 98 | 92 | 87 | 83 | 90 | 86 | 82 | 88 | 84 | 82 | 86 | 83 | 81 | 79 | | |
| 5 | 95 | 88 | 82 | 78 | 94 | 87 | 82 | 78 | 85 | 81 | 77 | 83 | 80 | 77 | 82 | 79 | 76 | 75 | | |
| 6 | 91 | 83 | 78 | 74 | 90 | 82 | 77 | 74 | 81 | 76 | 73 | 79 | 76 | 73 | 78 | 75 | 72 | 71 | | |
| 7 | 87 | 79 | 73 | 70 | 86 | 78 | 73 | 69 | 77 | 72 | 69 | 76 | 72 | 69 | 75 | 71 | 68 | 67 | | |
| 8 | 84 | 75 | 70 | 66 | 82 | 74 | 69 | 66 | 73 | 69 | 65 | 72 | 68 | 65 | 71 | 68 | 65 | 64 | | |
| 9 | 80 | 71 | 66 | 62 | 79 | 71 | 66 | 62 | 70 | 65 | 62 | 69 | 65 | 62 | 68 | 65 | 62 | 61 | | |
| 10 | 77 | 68 | 63 | 59 | 76 | 68 | 63 | 59 | 67 | 62 | 59 | 66 | 62 | 59 | 66 | 62 | 59 | 58 | | |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208473

CATALOG NUMBER: LD4B15D010 EU4B10208035 4LBNWH1

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 174.9 | 17.4 |
| 10°-20° | 328.1 | 32.6 |
| 20°-30° | 294.4 | 29.3 |
| 30°-40° | 168.9 | 16.8 |
| 40°-50° | 33.7 | 3.3 |
| 50°-60° | 4.3 | 0.4 |
| 60°-70° | 1.9 | 0.2 |
| 70°-80° | 0.2 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 797.4 | 79.2 |
| 0°-40° | 966.4 | 96.0 |
| 0°-60° | 1004.3 | 99.8 |
| 0°-90° | 1006.5 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1006.5 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2139 | |
| 5° | 1967 | 175 |
| 15° | 1178 | 328 |
| 25° | 636 | 294 |
| 35° | 268 | 169 |
| 45° | 36 | 34 |
| 55° | 5 | 4 |
| 65° | 2 | 2 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P208473

CATALOG NUMBER: LD4B15D010 EU4B10208035 4LBNWH1

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 2139.0 |
| 2.5° | 2095.6 |
| 5° | 1967.0 |
| 7.5° | 1779.3 |
| 10° | 1574.3 |
| 12.5° | 1372.7 |
| 15° | 1178.1 |
| 17.5° | 1007.8 |
| 20° | 861.9 |
| 22.5° | 740.2 |
| 25° | 636.0 |
| 27.5° | 552.6 |
| 30° | 460.5 |
| 32.5° | 366.6 |
| 35° | 267.6 |
| 37.5° | 182.4 |
| 40° | 112.9 |
| 42.5° | 67.8 |
| 45° | 36.5 |
| 47.5° | 15.6 |
| 50° | 7.0 |
| 52.5° | 5.2 |
| 55° | 5.2 |
| 57.5° | 3.5 |
| 60° | 3.5 |
| 62.5° | 1.7 |
| 65° | 1.7 |
| 67.5° | 1.7 |
| 70° | 1.7 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)