

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205725

Luminaire Tested: **LD4B30D010 EU4B30509040 4LBSH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205725
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30509040 4LBSH1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2486.9 lumens
Efficiency: N/A
Efficacy: 88.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205725

CATALOG NUMBER: LD4B30D010 EU4B30509040 4LBSH1

Luminous Intensity Polar Plot





TEST NUMBER: P205725

CATALOG NUMBER: LD4B30D010 EU4B30509040 4LBSH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205725

CATALOG NUMBER: LD4B30D010 EU4B30509040 4LBSH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.8	4.9
10°-20°	331.1	13.3
20°-30°	459.9	18.5
30°-40°	501.8	20.2
40°-50°	468.1	18.8
50°-60°	355.3	14.3
60°-70°	194.6	7.8
70°-80°	53.5	2.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	912.8	36.7
0°-40°	1414.6	56.9
0°-60°	2238.0	90.0
0°-90°	2486.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2486.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1301	
5°	1290	122
15°	1180	331
25°	999	460
35°	802	502
45°	608	468
55°	397	355
65°	194	195
75°	46	54
85°	0	1
90°	0	



TEST NUMBER: P205725

CATALOG NUMBER: LD4B30D010 EU4B30509040 4LBSH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1300.6
2.5°	1300.6
5°	1289.7
7.5°	1273.2
10°	1248.6
12.5°	1215.7
15°	1180.1
17.5°	1136.3
20°	1095.3
22.5°	1046.0
25°	999.4
27.5°	952.9
30°	900.8
32.5°	851.6
35°	802.3
37.5°	753.0
40°	706.4
42.5°	657.2
45°	607.9
47.5°	558.6
50°	503.8
52.5°	451.8
55°	397.0
57.5°	345.0
60°	293.0
62.5°	241.0
65°	194.4
67.5°	150.6
70°	112.3
72.5°	76.7
75°	46.5
77.5°	21.9
80°	5.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)