

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206344

Luminaire Tested: **LD4B30D010 EU4B30508050 4LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206344
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30508050 4LBCSMW1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3152.3 lumens
Efficiency: N/A
Efficacy: 112.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206344

CATALOG NUMBER: LD4B30D010 EU4B30508050 4LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P206344

CATALOG NUMBER: LD4B30D010 EU4B30508050 4LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87			87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74			74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63			63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55			55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48			48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42			42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37			37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33			33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30			30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27			27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206344

CATALOG NUMBER: LD4B30D010 EU4B30508050 4LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.0	3.9
10°-20°	347.3	11.0
20°-30°	522.4	16.6
30°-40°	619.1	19.6
40°-50°	616.1	19.5
50°-60°	496.7	15.8
60°-70°	300.5	9.5
70°-80°	111.5	3.5
80°-90°	16.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	991.7	31.5
0°-40°	1610.8	51.1
0°-60°	2723.7	86.4
0°-90°	3152.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3152.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1288	
5°	1282	122
15°	1230	347
25°	1135	522
35°	991	619
45°	802	616
55°	554	497
65°	302	300
75°	101	112
85°	13	17
90°	0	



TEST NUMBER: P206344

CATALOG NUMBER: LD4B30D010 EU4B30508050 4LBCSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1287.5
2.5°	1287.5
5°	1281.8
7.5°	1278.0
10°	1266.5
12.5°	1247.4
15°	1230.2
17.5°	1211.1
20°	1188.2
22.5°	1165.3
25°	1134.7
27.5°	1102.2
30°	1065.9
32.5°	1031.5
35°	991.4
37.5°	949.4
40°	899.7
42.5°	852.0
45°	802.3
47.5°	746.9
50°	685.8
52.5°	622.7
55°	554.0
57.5°	492.8
60°	424.1
62.5°	362.9
65°	301.8
67.5°	244.5
70°	191.0
72.5°	143.3
75°	101.2
77.5°	64.9
80°	38.2
82.5°	22.9
85°	13.4
87.5°	5.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)