

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205901

Luminaire Tested: **LD4B15D010 EU4B10208040 4LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205901
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10208040 4LBSGPH1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1395.6 lumens
Efficiency: N/A
Efficacy: 97.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205901

CATALOG NUMBER: LD4B15D010 EU4B10208040 4LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P205901

CATALOG NUMBER: LD4B15D010 EU4B10208040 4LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88			88																
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			76																
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66			66																
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57			57																
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50			50																
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45			45																
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40			40																
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36			36																
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32			32																
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30			30																

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205901

CATALOG NUMBER: LD4B15D010 EU4B10208040 4LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.0	4.4
10°-20°	171.3	12.3
20°-30°	249.9	17.9
30°-40°	284.9	20.4
40°-50°	273.3	19.6
50°-60°	209.3	15.0
60°-70°	114.9	8.2
70°-80°	30.5	2.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	482.2	34.6
0°-40°	767.1	55.0
0°-60°	1249.8	89.5
0°-90°	1395.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1395.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	648	
5°	643	61
15°	608	171
25°	543	250
35°	456	285
45°	355	273
55°	234	209
65°	116	115
75°	27	31
85°	0	0
90°	0	



TEST NUMBER: P205901

CATALOG NUMBER: LD4B15D010 EU4B10208040 4LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	648.2
2.5°	646.5
5°	643.2
7.5°	638.2
10°	631.5
12.5°	619.7
15°	608.0
17.5°	594.6
20°	579.5
22.5°	561.1
25°	542.7
27.5°	524.3
30°	500.8
32.5°	479.0
35°	455.6
37.5°	432.1
40°	408.7
42.5°	383.6
45°	355.1
47.5°	326.6
50°	296.5
52.5°	264.6
55°	234.5
57.5°	204.3
60°	172.5
62.5°	142.4
65°	115.6
67.5°	88.8
70°	65.3
72.5°	43.5
75°	26.8
77.5°	11.7
80°	3.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)