

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207147

Luminaire Tested: **LD4B15D010 EU4B10209040 4LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207147
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10209040 4LBMH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 975.8 lumens
Efficiency: N/A
Efficacy: 68.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207147

CATALOG NUMBER: LD4B15D010 EU4B10209040 4LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P207147

CATALOG NUMBER: LD4B15D010 EU4B10209040 4LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85		
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79		
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73		
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67		
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62		
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58		
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54		
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50		
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207147

CATALOG NUMBER: LD4B15D010 EU4B10209040 4LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.0	9.1
10°-20°	233.6	23.9
20°-30°	300.2	30.8
30°-40°	225.9	23.1
40°-50°	90.7	9.3
50°-60°	25.8	2.6
60°-70°	8.2	0.8
70°-80°	2.3	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	622.8	63.8
0°-40°	848.7	87.0
0°-60°	965.1	98.9
0°-90°	975.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	975.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	968	
5°	950	89
15°	834	234
25°	663	300
35°	362	226
45°	112	91
55°	26	26
65°	7	8
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P207147

CATALOG NUMBER: LD4B15D010 EU4B10209040 4LBMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	967.6
2.5°	961.7
5°	950.0
7.5°	927.9
10°	899.9
12.5°	866.0
15°	833.6
17.5°	796.8
20°	757.0
22.5°	714.3
25°	662.8
27.5°	600.9
30°	528.7
32.5°	447.7
35°	362.3
37.5°	282.8
40°	212.1
42.5°	156.1
45°	111.9
47.5°	76.6
50°	53.0
52.5°	36.8
55°	26.5
57.5°	19.1
60°	14.7
62.5°	10.3
65°	7.4
67.5°	5.9
70°	4.4
72.5°	2.9
75°	1.5
77.5°	1.5
80°	1.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)