

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206735

Luminaire Tested: **LD4B15D010 EU4B10209040 4LBWWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206735  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B15D010 EU4B10209040 4LBWWH1  
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W  
DL3-15.28W DLE-15.432W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1126.0 lumens  
Efficiency: N/A  
Efficacy: 78.7 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206735

CATALOG NUMBER: LD4B15D010 EU4B10209040 4LBWWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P206735

CATALOG NUMBER: LD4B15D010 EU4B10209040 4LBWWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	85	84	84	84	84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69	69	69	69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63	63	63	63
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58	58	58	58
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53	53	53	53
8	73	62	56	51	72	62	55	51	61	55	51	60	54	50	59	54	50	49	49	49	49
9	69	58	51	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45	45	45	45
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41	41	41	41

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206735

CATALOG NUMBER: LD4B15D010 EU4B10209040 4LBWWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.2	6.1
10°-20°	211.0	18.7
20°-30°	324.6	28.8
30°-40°	313.2	27.8
40°-50°	163.3	14.5
50°-60°	34.4	3.1
60°-70°	8.0	0.7
70°-80°	3.1	0.3
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	603.8	53.6
0°-40°	917.0	81.4
0°-60°	1114.7	99.0
0°-90°	1126.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1126.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	704	
5°	710	68
15°	747	211
25°	711	325
35°	508	313
45°	208	163
55°	31	34
65°	7	8
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P206735

CATALOG NUMBER: LD4B15D010 EU4B10209040 4LBWWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	704.0
2.5°	705.5
5°	709.9
7.5°	715.8
10°	724.6
12.5°	736.4
15°	746.7
17.5°	752.6
20°	748.2
22.5°	739.4
25°	711.4
27.5°	677.5
30°	633.3
32.5°	574.4
35°	508.1
37.5°	436.0
40°	360.8
42.5°	285.7
45°	207.7
47.5°	139.9
50°	89.8
52.5°	54.5
55°	30.9
57.5°	19.1
60°	13.3
62.5°	10.3
65°	7.4
67.5°	5.9
70°	4.4
72.5°	4.4
75°	2.9
77.5°	1.5
80°	1.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)