

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P252024

Luminaire Tested: **LD4B40D010 EU4B30508027 4LBBA1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P252024
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-3)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30508027 4LBBA1MW
Description: PORTFOLIO 4 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4682.1 lumens
Efficiency: N/A
Efficacy: 108.8 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.99
Luminous Opening: Circular (Dia: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 43.02
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P252024

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBBA1MW

Luminous Intensity Polar Plot





TEST NUMBER: P252024

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBBA1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78				78
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69				69
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62				62
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56				56
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51				51
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46				46
8	69	58	50	45	68	57	50	45	56	49	45	54	49	45	53	48	44	43				43
9	65	54	46	42	64	53	46	42	52	46	41	51	45	41	50	45	41	39				39
10	62	50	43	39	61	50	43	38	49	43	38	48	42	38	47	42	38	37				37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	319107
5°	315836
10°	306355
15°	294061
20°	280833
25°	262639
30°	228615
35°	176415
40°	130518
45°	102708
50°	88226
55°	80216
60°	73133
65°	67683
70°	62546
75°	58629
80°	54440
85°	51326



TEST NUMBER: P252024

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBBA1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	303.9	6.5
10°-20°	819.1	17.5
20°-30°	1108.3	23.7
30°-40°	931.3	19.9
40°-50°	589.3	12.6
50°-60°	423.3	9.0
60°-70°	291.3	6.2
70°-80°	164.9	3.5
80°-90°	50.7	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2231.3	47.7
0°-40°	3162.6	67.5
0°-60°	4175.1	89.2
0°-90°	4682.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4682.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3274	
5°	3228	304
15°	2914	819
25°	2442	1108
35°	1483	931
45°	745	589
55°	472	423
65°	294	291
75°	156	165
85°	46	51
90°	0	



TEST NUMBER: P252024

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBBA1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3274.3
2.5°	3264.1
5°	3228.4
7.5°	3169.7
10°	3095.7
12.5°	3008.9
15°	2914.5
17.5°	2812.4
20°	2707.8
22.5°	2585.3
25°	2442.4
27.5°	2258.6
30°	2031.5
32.5°	1766.1
35°	1482.8
37.5°	1232.7
40°	1025.9
42.5°	865.2
45°	745.2
47.5°	653.3
50°	581.9
52.5°	523.2
55°	472.1
57.5°	421.1
60°	375.2
62.5°	331.8
65°	293.5
67.5°	255.2
70°	219.5
72.5°	186.3
75°	155.7
77.5°	125.1
80°	97.0
82.5°	71.5
85°	45.9
87.5°	20.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)