

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P251989

Luminaire Tested: **LD4B15D010 EU4B10208050 4LBBA1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P251989
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-3)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10208050 4LBBA1MW
Description: PORTFOLIO 4 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1854.0 lumens
Efficiency: N/A
Efficacy: 128.8 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.99
Luminous Opening: Circular (Dia: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 14.39
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251989

CATALOG NUMBER: LD4B15D010 EU4B10208050 4LBBA1MW

Luminous Intensity Polar Plot





TEST NUMBER: P251989

CATALOG NUMBER: LD4B15D010 EU4B10208050 4LBBA1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78				78
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69				69
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62				62
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56				56
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51				51
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46				46
8	69	58	50	45	68	57	50	45	56	49	45	54	49	45	53	48	44	43				43
9	65	54	46	42	64	53	46	42	52	46	41	51	45	41	50	45	41	39				39
10	62	50	43	39	61	50	43	38	49	43	38	48	42	38	47	42	38	37				37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	126364
5°	125066
10°	121307
15°	116444
20°	111201
25°	103995
30°	90523
35°	69862
40°	51690
45°	40673
50°	34933
55°	31774
60°	28965
65°	26796
70°	24762
75°	23195
80°	21552
85°	20351



TEST NUMBER: P251989

CATALOG NUMBER: LD4B15D010 EU4B10208050 4LBBA1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.3	6.5
10°-20°	324.3	17.5
20°-30°	438.9	23.7
30°-40°	368.8	19.9
40°-50°	233.4	12.6
50°-60°	167.6	9.0
60°-70°	115.4	6.2
70°-80°	65.3	3.5
80°-90°	20.1	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	883.5	47.7
0°-40°	1252.3	67.5
0°-60°	1653.3	89.2
0°-90°	1854.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1854.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1297	
5°	1278	120
15°	1154	324
25°	967	439
35°	587	369
45°	295	233
55°	187	168
65°	116	115
75°	62	65
85°	18	20
90°	0	



TEST NUMBER: P251989

CATALOG NUMBER: LD4B15D010 EU4B10208050 4LBBA1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1296.6
2.5°	1292.5
5°	1278.4
7.5°	1255.2
10°	1225.8
12.5°	1191.5
15°	1154.1
17.5°	1113.7
20°	1072.2
22.5°	1023.7
25°	967.1
27.5°	894.4
30°	804.4
32.5°	699.3
35°	587.2
37.5°	488.1
40°	406.3
42.5°	342.6
45°	295.1
47.5°	258.7
50°	230.4
52.5°	207.2
55°	187.0
57.5°	166.7
60°	148.6
62.5°	131.4
65°	116.2
67.5°	101.1
70°	86.9
72.5°	73.8
75°	61.6
77.5°	49.5
80°	38.4
82.5°	28.3
85°	18.2
87.5°	8.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)