

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207280

Luminaire Tested: **LD4B40D010 EU4B30508027 4LBMWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P207280  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B40D010 EU4B30508027 4LBMWH1  
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W  
DL3-44.71W DLE-39.33W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3002.4 lumens  
Efficiency: N/A  
Efficacy: 71.8 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.87  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P207280

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBMWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P207280

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBMWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	105	105	103	101	101	100	98	98	96	95	94			
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87			
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71			
6	88	79	73	69	87	79	73	69	77	72	68	76	71	68	74	71	68	66			
7	84	75	69	65	82	74	68	64	73	68	64	72	67	64	70	66	63	62			
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	59	58			
9	76	66	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55			
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P207280

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBMWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	329.4	11.0
10°-20°	846.9	28.2
20°-30°	993.6	33.1
30°-40°	628.8	20.9
40°-50°	168.4	5.6
50°-60°	23.5	0.8
60°-70°	8.7	0.3
70°-80°	2.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2170.0	72.3
0°-40°	2798.8	93.2
0°-60°	2990.8	99.6
0°-90°	3002.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3002.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3566	
5°	3508	329
15°	3034	847
25°	2195	994
35°	998	629
45°	191	168
55°	22	24
65°	9	9
75°	4	3
85°	0	0
90°	0	



TEST NUMBER: P207280

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBMWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3565.8
2.5°	3552.5
5°	3508.2
7.5°	3437.2
10°	3335.2
12.5°	3202.1
15°	3033.6
17.5°	2860.6
20°	2652.2
22.5°	2439.3
25°	2195.4
27.5°	1929.3
30°	1632.1
32.5°	1308.4
35°	997.9
37.5°	722.9
40°	496.7
42.5°	319.3
45°	190.7
47.5°	106.4
50°	57.7
52.5°	31.0
55°	22.2
57.5°	17.7
60°	13.3
62.5°	13.3
65°	8.9
67.5°	4.4
70°	4.4
72.5°	4.4
75°	4.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)