

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206765

Luminaire Tested: **LD4B40D010 EU4B30508027 4LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206765
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30508027 4LBWWH1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3392.7 lumens
Efficiency: N/A
Efficacy: 81.2 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206765

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P206765

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	85	84	84	84	84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69	69	69	69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63	63	63	63
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58	58	58	58
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53	53	53	53
8	73	62	56	51	72	62	55	51	61	55	51	60	54	50	59	54	50	49	49	49	49
9	69	58	51	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45	45	45	45
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41	41	41	41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206765

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	205.5	6.1
10°-20°	635.8	18.7
20°-30°	978.1	28.8
30°-40°	943.7	27.8
40°-50°	492.0	14.5
50°-60°	103.6	3.1
60°-70°	24.1	0.7
70°-80°	9.3	0.3
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1819.4	53.6
0°-40°	2763.1	81.4
0°-60°	3358.7	99.0
0°-90°	3392.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3392.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2121	
5°	2139	206
15°	2250	636
25°	2144	978
35°	1531	944
45°	626	492
55°	93	104
65°	22	24
75°	9	9
85°	0	1
90°	0	



TEST NUMBER: P206765

CATALOG NUMBER: LD4B40D010 EU4B30508027 4LBWWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2121.3
2.5°	2125.7
5°	2139.0
7.5°	2156.8
10°	2183.4
12.5°	2218.9
15°	2250.0
17.5°	2267.7
20°	2254.4
22.5°	2227.8
25°	2143.5
27.5°	2041.4
30°	1908.3
32.5°	1730.7
35°	1531.0
37.5°	1313.6
40°	1087.3
42.5°	860.9
45°	625.7
47.5°	421.6
50°	270.7
52.5°	164.2
55°	93.2
57.5°	57.7
60°	39.9
62.5°	31.1
65°	22.2
67.5°	17.8
70°	13.3
72.5°	13.3
75°	8.9
77.5°	4.4
80°	4.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)