

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205735

Luminaire Tested: **LD4B40D010 EU4B30509027 4LBSH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205735
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30509027 4LBSH1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3297.3 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205735

CATALOG NUMBER: LD4B40D010 EU4B30509027 4LBSH1

Luminous Intensity Polar Plot





TEST NUMBER: P205735

CATALOG NUMBER: LD4B40D010 EU4B30509027 4LBSH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205735

CATALOG NUMBER: LD4B40D010 EU4B30509027 4LBSH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.5	4.9
10°-20°	439.0	13.3
20°-30°	609.7	18.5
30°-40°	665.3	20.2
40°-50°	620.7	18.8
50°-60°	471.1	14.3
60°-70°	258.0	7.8
70°-80°	71.0	2.2
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1210.3	36.7
0°-40°	1875.6	56.9
0°-60°	2967.4	90.0
0°-90°	3297.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3297.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1724	
5°	1710	162
15°	1565	439
25°	1325	610
35°	1064	665
45°	806	621
55°	526	471
65°	258	258
75°	62	71
85°	0	1
90°	0	



TEST NUMBER: P205735

CATALOG NUMBER: LD4B40D010 EU4B30509027 4LBSH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1724.5
2.5°	1724.5
5°	1710.0
7.5°	1688.2
10°	1655.5
12.5°	1611.9
15°	1564.7
17.5°	1506.7
20°	1452.2
22.5°	1386.9
25°	1325.1
27.5°	1263.4
30°	1194.4
32.5°	1129.1
35°	1063.7
37.5°	998.4
40°	936.7
42.5°	871.3
45°	806.0
47.5°	740.6
50°	668.0
52.5°	599.0
55°	526.4
57.5°	457.4
60°	388.5
62.5°	319.5
65°	257.8
67.5°	199.7
70°	148.9
72.5°	101.7
75°	61.7
77.5°	29.0
80°	7.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)