

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207451

Luminaire Tested: **LD4B15D010 EU4B10208050 4LBMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207451
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10208050 4LBMB1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 637.4 lumens
Efficiency: N/A
Efficacy: 44.6 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.87
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207451

CATALOG NUMBER: LD4B15D010 EU4B10208050 4LBMB1

Luminous Intensity Polar Plot





TEST NUMBER: P207451

CATALOG NUMBER: LD4B15D010 EU4B10208050 4LBMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94																											
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																											
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82																											
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	77																											
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72																											
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																											
7	84	75	70	65	83	75	69	65	73	68	65	72	68	65	71	67	64	63																											
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59																											
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56																											
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52																											

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207451

CATALOG NUMBER: LD4B15D010 EU4B10208050 4LBMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.3	11.3
10°-20°	179.7	28.2
20°-30°	217.4	34.1
30°-40°	138.7	21.8
40°-50°	28.9	4.5
50°-60°	0.4	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	469.4	73.6
0°-40°	608.1	95.4
0°-60°	637.4	100.0
0°-90°	637.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	637.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	800	
5°	776	72
15°	642	180
25°	484	217
35°	222	139
45°	30	29
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P207451

CATALOG NUMBER: LD4B15D010 EU4B10208050 4LBMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	800.1
2.5°	791.3
5°	775.5
7.5°	752.6
10°	719.2
12.5°	678.8
15°	641.8
17.5°	604.9
20°	564.5
22.5°	525.8
25°	483.6
27.5°	427.3
30°	365.8
32.5°	293.7
35°	221.6
37.5°	154.7
40°	102.0
42.5°	59.8
45°	29.9
47.5°	12.3
50°	3.5
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)