

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207600

Luminaire Tested: **LD4B40D010 EU4B30509727 4LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207600
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30509727 4LBMMW1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2284.6 lumens
Efficiency: N/A
Efficacy: 54.7 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207600

CATALOG NUMBER: LD4B40D010 EU4B30509727 4LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P207600

CATALOG NUMBER: LD4B40D010 EU4B30509727 4LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89			
2	104	98	92	88	102	96	91	87	93	89	85	89	86	83	87	84	81	80			
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71			
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	69	66	64			
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58			
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53			
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49			
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45			
9	67	55	48	44	66	55	48	44	54	48	44	53	47	43	52	47	43	42			
10	63	52	45	41	62	51	45	41	51	45	40	50	44	40	49	44	40	39			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207600

CATALOG NUMBER: LD4B40D010 EU4B30509727 4LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.8	7.0
10°-20°	430.9	18.9
20°-30°	573.0	25.1
30°-40°	468.7	20.5
40°-50°	273.0	11.9
50°-60°	181.0	7.9
60°-70°	119.1	5.2
70°-80°	62.8	2.7
80°-90°	15.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1164.7	51.0
0°-40°	1633.4	71.5
0°-60°	2087.4	91.4
0°-90°	2284.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2284.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1734	
5°	1714	161
15°	1536	431
25°	1258	573
35°	748	469
45°	344	273
55°	202	181
65°	119	119
75°	60	63
85°	13	15
90°	0	



TEST NUMBER: P207600

CATALOG NUMBER: LD4B40D010 EU4B30509727 4LBMMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1734.3
2.5°	1731.0
5°	1714.4
7.5°	1674.7
10°	1631.7
12.5°	1592.0
15°	1535.7
17.5°	1472.8
20°	1419.9
22.5°	1347.0
25°	1257.7
27.5°	1161.7
30°	1039.2
32.5°	893.6
35°	748.0
37.5°	615.6
40°	499.8
42.5°	410.4
45°	344.2
47.5°	291.3
50°	254.8
52.5°	225.1
55°	201.9
57.5°	178.7
60°	155.6
62.5°	139.0
65°	119.1
67.5°	102.6
70°	86.1
72.5°	72.8
75°	59.6
77.5°	46.3
80°	33.1
82.5°	23.2
85°	13.2
87.5°	3.3
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)