

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207291

Luminaire Tested: **LD4B40D010 EU4B30509727 4LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207291
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30509727 4LBMWH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2241.5 lumens
Efficiency: N/A
Efficacy: 53.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.87
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207291

CATALOG NUMBER: LD4B40D010 EU4B30509727 4LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P207291

CATALOG NUMBER: LD4B40D010 EU4B30509727 4LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	105	105	103	101	101	100	98	98	96	95	94			
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87			
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71			
6	88	79	73	69	87	79	73	69	77	72	68	76	71	68	74	71	68	66			
7	84	75	69	65	82	74	68	64	73	68	64	72	67	64	70	66	63	62			
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	59	58			
9	76	66	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55			
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207291

CATALOG NUMBER: LD4B40D010 EU4B30509727 4LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.9	11.0
10°-20°	632.3	28.2
20°-30°	741.8	33.1
30°-40°	469.5	20.9
40°-50°	125.7	5.6
50°-60°	17.6	0.8
60°-70°	6.5	0.3
70°-80°	2.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1620.1	72.3
0°-40°	2089.5	93.2
0°-60°	2232.8	99.6
0°-90°	2241.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2241.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2662	
5°	2619	246
15°	2265	632
25°	1639	742
35°	745	469
45°	142	126
55°	17	18
65°	7	6
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P207291

CATALOG NUMBER: LD4B40D010 EU4B30509727 4LBMWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2662.1
2.5°	2652.2
5°	2619.1
7.5°	2566.1
10°	2490.0
12.5°	2390.6
15°	2264.8
17.5°	2135.7
20°	1980.1
22.5°	1821.1
25°	1639.0
27.5°	1440.3
30°	1218.5
32.5°	976.8
35°	745.0
37.5°	539.7
40°	370.8
42.5°	238.4
45°	142.4
47.5°	79.5
50°	43.0
52.5°	23.2
55°	16.6
57.5°	13.2
60°	9.9
62.5°	9.9
65°	6.6
67.5°	3.3
70°	3.3
72.5°	3.3
75°	3.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)