

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207657

Luminaire Tested: **LD4B15D010 EU4B10208050 4LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207657
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10208050 4LBNH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 967.6 lumens
Efficiency: N/A
Efficacy: 67.7 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207657

CATALOG NUMBER: LD4B15D010 EU4B10208050 4LBNH1

Luminous Intensity Polar Plot





TEST NUMBER: P207657

CATALOG NUMBER: LD4B15D010 EU4B10208050 4LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	76	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207657

CATALOG NUMBER: LD4B15D010 EU4B10208050 4LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.6	11.3
10°-20°	265.9	27.5
20°-30°	308.7	31.9
30°-40°	204.4	21.1
40°-50°	57.3	5.9
50°-60°	14.4	1.5
60°-70°	5.4	0.6
70°-80°	1.9	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	684.1	70.7
0°-40°	888.5	91.8
0°-60°	960.3	99.2
0°-90°	967.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	967.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1215	
5°	1183	110
15°	952	266
25°	677	309
35°	328	204
45°	67	57
55°	16	14
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P207657

CATALOG NUMBER: LD4B15D010 EU4B10208050 4LBNH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1214.7
2.5°	1209.5
5°	1183.2
7.5°	1137.6
10°	1081.5
12.5°	1018.4
15°	951.8
17.5°	886.9
20°	815.1
22.5°	748.5
25°	676.6
27.5°	608.2
30°	520.6
32.5°	427.7
35°	327.8
37.5°	234.9
40°	159.5
42.5°	103.4
45°	66.6
47.5°	40.3
50°	26.3
52.5°	19.3
55°	15.8
57.5°	12.3
60°	8.8
62.5°	7.0
65°	5.3
67.5°	3.5
70°	3.5
72.5°	1.8
75°	1.8
77.5°	1.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)