

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206627

Luminaire Tested: **LD4B15D010 EU4B10208050 4LBWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206627  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B15D010 EU4B10208050 4LBWH1  
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W  
DL3-15.28W DLE-15.432W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1294.0 lumens  
Efficiency: N/A  
Efficacy: 90.5 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206627

CATALOG NUMBER: LD4B15D010 EU4B10208050 4LBWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P206627

CATALOG NUMBER: LD4B15D010 EU4B10208050 4LBWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82				82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74				74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67				67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61				61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55				55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50				50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46				46
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43				43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39				39

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206627

CATALOG NUMBER: LD4B15D010 EU4B10208050 4LBWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	79.4	6.1
10°-20°	228.9	17.7
20°-30°	337.8	26.1
30°-40°	333.3	25.8
40°-50°	204.0	15.8
50°-60°	78.2	6.0
60°-70°	24.4	1.9
70°-80°	7.2	0.6
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	646.1	49.9
0°-40°	979.4	75.7
0°-60°	1261.5	97.5
0°-90°	1294.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1294.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	834	
5°	834	79
15°	811	229
25°	739	338
35°	541	333
45°	262	204
55°	82	78
65°	23	24
75°	7	7
85°	0	1
90°	0	



TEST NUMBER: P206627

CATALOG NUMBER: LD4B15D010 EU4B10208050 4LBWH1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	834.1
2.5°	835.9
5°	834.1
7.5°	832.3
10°	827.1
12.5°	820.0
15°	811.3
17.5°	800.7
20°	784.9
22.5°	767.4
25°	739.3
27.5°	704.2
30°	660.3
32.5°	605.8
35°	540.8
37.5°	468.9
40°	395.1
42.5°	326.6
45°	261.6
47.5°	203.7
50°	154.5
52.5°	114.1
55°	82.5
57.5°	57.9
60°	42.1
62.5°	31.6
65°	22.8
67.5°	17.6
70°	12.3
72.5°	8.8
75°	7.0
77.5°	3.5
80°	3.5
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)