

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P252073

Luminaire Tested: **LD4B15D010 EU4B10209050 4LBBA1MB**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P252073  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-4)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B15D010 EU4B10209050 4LBBA1MB  
Description: PORTFOLIO 4 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE BLACK TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 650.9 lumens  
Efficiency: N/A  
Efficacy: 45.2 lumens/watt  
Spacing Criteria (0/90/45): 1.04 / 1.04 / 0.94  
Luminous Opening: Circular (Dia: 0.38' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.39  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P252073

CATALOG NUMBER: LD4B15D010 EU4B10209050 4LBBA1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P252073

CATALOG NUMBER: LD4B15D010 EU4B10209050 4LBBA1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	88	83	79	86	82	78	84	81	77	82	79	77	75			
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65			
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61			
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57			
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53			
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	63455
5°	63277
10°	62662
15°	61658
20°	59853
25°	55294
30°	44856
35°	27804
40°	13078
45°	4562
50°	1289
55°	867
60°	663
65°	577
70°	484
75°	301
80°	449
85°	0



TEST NUMBER: P252073

CATALOG NUMBER: LD4B15D010 EU4B10209050 4LBBA1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	61.3	9.4
10°-20°	171.8	26.4
20°-30°	230.9	35.5
30°-40°	147.5	22.7
40°-50°	31.3	4.8
50°-60°	4.7	0.7
60°-70°	2.3	0.4
70°-80°	1.0	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	464.0	71.3
0°-40°	611.4	93.9
0°-60°	647.5	99.5
0°-90°	650.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	650.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	651	
5°	647	61
15°	611	172
25°	514	231
35°	234	147
45°	33	31
55°	5	5
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P252073

CATALOG NUMBER: LD4B15D010 EU4B10209050 4LBBA1MB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	651.1
2.5°	650.2
5°	646.8
7.5°	640.9
10°	633.2
12.5°	623.0
15°	611.1
17.5°	595.8
20°	577.1
22.5°	550.8
25°	514.2
27.5°	463.2
30°	398.6
32.5°	318.7
35°	233.7
37.5°	159.8
40°	102.8
42.5°	61.2
45°	33.1
47.5°	17.0
50°	8.5
52.5°	5.9
55°	5.1
57.5°	4.2
60°	3.4
62.5°	2.5
65°	2.5
67.5°	1.7
70°	1.7
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)