

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207560

Luminaire Tested: **LD4B15D010 EU4B10209050 4LBMMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P207560  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B15D010 EU4B10209050 4LBMMW1  
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W  
DL3-15.28W DLE-15.432W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1019.4 lumens  
Efficiency: N/A  
Efficacy: 71.3 lumens/watt  
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P207560

CATALOG NUMBER: LD4B15D010 EU4B10209050 4LBMMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P207560

CATALOG NUMBER: LD4B15D010 EU4B10209050 4LBMMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89																			
2	104	98	92	88	102	96	91	87	93	89	85	89	86	83	87	84	81	80																			
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71																			
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	69	66	64																			
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58																			
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53																			
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49																			
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45																			
9	67	55	48	44	66	55	48	44	54	48	44	53	47	43	52	47	43	42																			
10	63	52	45	41	62	51	45	41	51	45	40	50	44	40	49	44	40	39																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P207560

CATALOG NUMBER: LD4B15D010 EU4B10209050 4LBMMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	71.7	7.0
10°-20°	192.3	18.9
20°-30°	255.7	25.1
30°-40°	209.1	20.5
40°-50°	121.8	11.9
50°-60°	80.8	7.9
60°-70°	53.1	5.2
70°-80°	28.0	2.8
80°-90°	6.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	519.7	51.0
0°-40°	728.9	71.5
0°-60°	931.4	91.4
0°-90°	1019.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1019.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	774	
5°	765	72
15°	685	192
25°	561	256
35°	334	209
45°	154	122
55°	90	81
65°	53	53
75°	27	28
85°	6	7
90°	0	



TEST NUMBER: P207560

CATALOG NUMBER: LD4B15D010 EU4B10209050 4LBMMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	773.9
2.5°	772.4
5°	765.0
7.5°	747.3
10°	728.1
12.5°	710.4
15°	685.3
17.5°	657.2
20°	633.6
22.5°	601.1
25°	561.2
27.5°	518.4
30°	463.7
32.5°	398.7
35°	333.8
37.5°	274.7
40°	223.0
42.5°	183.1
45°	153.6
47.5°	130.0
50°	113.7
52.5°	100.4
55°	90.1
57.5°	79.7
60°	69.4
62.5°	62.0
65°	53.2
67.5°	45.8
70°	38.4
72.5°	32.5
75°	26.6
77.5°	20.7
80°	14.8
82.5°	10.3
85°	5.9
87.5°	1.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)