

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208008

Luminaire Tested: **LD4B40D010 EU4B30509030 4LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208008
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30509030 4LBNMW1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2490.5 lumens
Efficiency: N/A
Efficacy: 59.6 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.95
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208008

CATALOG NUMBER: LD4B40D010 EU4B30509030 4LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P208008

CATALOG NUMBER: LD4B40D010 EU4B30509030 4LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	105	103	109	106	104	101	102	100	98	98	97	95	95	94	92	90		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	80	96	89	83	79	86	82	78	84	80	76	81	78	75	73		
4	92	83	76	71	90	82	76	71	80	74	70	78	73	69	76	72	68	67		
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61		
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56		
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	62	57	53	52		
8	73	62	55	50	71	61	55	50	60	54	50	59	53	49	58	53	49	48		
9	69	58	51	46	68	57	51	46	56	50	46	55	50	46	54	49	46	44		
10	65	54	48	43	64	54	47	43	53	47	43	52	47	43	51	46	43	41		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208008

CATALOG NUMBER: LD4B40D010 EU4B30509030 4LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.5	7.8
10°-20°	511.4	20.5
20°-30°	673.1	27.0
30°-40°	523.9	21.0
40°-50°	254.5	10.2
50°-60°	160.8	6.5
60°-70°	103.7	4.2
70°-80°	54.2	2.2
80°-90°	13.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1379.9	55.4
0°-40°	1903.9	76.4
0°-60°	2319.1	93.1
0°-90°	2490.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2490.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2125	
5°	2085	195
15°	1824	511
25°	1484	673
35°	839	524
45°	316	254
55°	178	161
65°	103	104
75°	51	54
85°	12	13
90°	0	



TEST NUMBER: P208008

CATALOG NUMBER: LD4B40D010 EU4B30509030 4LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2124.6
2.5°	2112.7
5°	2085.0
7.5°	2037.5
10°	1974.2
12.5°	1903.0
15°	1823.9
17.5°	1740.8
20°	1653.8
22.5°	1570.7
25°	1483.6
27.5°	1372.9
30°	1222.5
32.5°	1044.5
35°	838.7
37.5°	648.8
40°	502.5
42.5°	391.7
45°	316.5
47.5°	257.2
50°	225.5
52.5°	201.8
55°	178.0
57.5°	158.3
60°	138.5
62.5°	118.7
65°	102.9
67.5°	91.0
70°	75.2
72.5°	63.3
75°	51.4
77.5°	39.6
80°	27.7
82.5°	19.8
85°	11.9
87.5°	4.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)