

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207807

Luminaire Tested: **LD4B40D010 EU4B30509730 4LBNGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P207807  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B40D010 EU4B30509730 4LBNGPH1  
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM  
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W  
DL3-44.71W DLE-39.33W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1429.4 lumens  
Efficiency: N/A  
Efficacy: 34.2 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.88  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P207807

CATALOG NUMBER: LD4B40D010 EU4B30509730 4LBNGPH1

### Luminous Intensity Polar Plot





TEST NUMBER: P207807

CATALOG NUMBER: LD4B40D010 EU4B30509730 4LBNGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	68	63	60	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	52	51			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P207807

CATALOG NUMBER: LD4B40D010 EU4B30509730 4LBNGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	155.8	10.9
10°-20°	390.7	27.3
20°-30°	476.1	33.3
30°-40°	314.1	22.0
40°-50°	72.3	5.1
50°-60°	13.9	1.0
60°-70°	5.1	0.4
70°-80°	1.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1022.6	71.5
0°-40°	1336.7	93.5
0°-60°	1422.9	99.5
0°-90°	1429.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1429.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1714	
5°	1672	156
15°	1399	391
25°	1046	476
35°	502	314
45°	80	72
55°	14	14
65°	4	5
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P207807

CATALOG NUMBER: LD4B40D010 EU4B30509730 4LBNGPH1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1714.1
2.5°	1710.6
5°	1672.5
7.5°	1620.6
10°	1551.3
12.5°	1482.1
15°	1399.0
17.5°	1312.4
20°	1222.4
22.5°	1142.7
25°	1045.8
27.5°	948.8
30°	824.2
32.5°	671.8
35°	502.1
37.5°	349.7
40°	225.1
42.5°	138.5
45°	79.6
47.5°	41.6
50°	24.2
52.5°	20.8
55°	13.9
57.5°	10.4
60°	10.4
62.5°	6.9
65°	3.5
67.5°	3.5
70°	3.5
72.5°	3.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)