

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206849

Luminaire Tested: **LD4B20D010 EU4B10209030 4LBWGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206849  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B20D010 EU4B10209030 4LBWGPH1  
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM  
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W  
DL3-21.8 6W DLE-22.46W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1132.1 lumens  
Efficiency: N/A  
Efficacy: 54.4 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206849

CATALOG NUMBER: LD4B20D010 EU4B10209030 4LBWGPH1

### Luminous Intensity Polar Plot





TEST NUMBER: P206849

CATALOG NUMBER: LD4B20D010 EU4B10209030 4LBWGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92				92															
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83				83															
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	77	76				76															
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69				69															
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63				63															
6	83	72	65	61	81	71	65	60	70	64	60	68	63	59	67	63	59	57				57															
7	78	67	60	55	76	66	60	55	65	59	55	64	58	55	63	58	54	53				53															
8	73	62	56	51	72	62	55	51	61	55	50	59	54	50	58	54	50	48				48															
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45				45															
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41				41															

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206849

CATALOG NUMBER: LD4B20D010 EU4B10209030 4LBWGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	76.9	6.8
10°-20°	217.8	19.2
20°-30°	312.4	27.6
30°-40°	294.1	26.0
40°-50°	162.4	14.3
50°-60°	52.1	4.6
60°-70°	13.1	1.2
70°-80°	3.1	0.3
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	607.0	53.6
0°-40°	901.1	79.6
0°-60°	1115.7	98.5
0°-90°	1132.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1132.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	815	
5°	811	77
15°	772	218
25°	685	312
35°	477	294
45°	206	162
55°	53	52
65°	12	13
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P206849

CATALOG NUMBER: LD4B20D010 EU4B10209030 4LBWGPH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	814.8
2.5°	808.9
5°	810.9
7.5°	805.0
10°	795.2
12.5°	785.4
15°	771.6
17.5°	759.8
20°	740.2
22.5°	712.7
25°	685.2
27.5°	647.9
30°	598.8
32.5°	543.9
35°	477.1
37.5°	406.4
40°	333.8
42.5°	267.0
45°	206.2
47.5°	155.1
50°	111.9
52.5°	78.5
55°	53.0
57.5°	35.3
60°	25.5
62.5°	17.7
65°	11.8
67.5°	7.9
70°	5.9
72.5°	3.9
75°	2.0
77.5°	2.0
80°	2.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)