

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206777

Luminaire Tested: **LD4B40D010 EU4B30509730 4LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206777
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30509730 4LBWWH1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2647.6 lumens
Efficiency: N/A
Efficacy: 63.3 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206777

CATALOG NUMBER: LD4B40D010 EU4B30509730 4LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P206777

CATALOG NUMBER: LD4B40D010 EU4B30509730 4LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	87	85	84	84	84	84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69	69	69	69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63	63	63	63
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58	58	58	58
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53	53	53	53
8	73	62	56	51	72	62	55	51	61	55	51	60	54	50	59	54	50	49	49	49	49
9	69	58	51	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45	45	45	45
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41	41	41	41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206777

CATALOG NUMBER: LD4B40D010 EU4B30509730 4LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.4	6.1
10°-20°	496.2	18.7
20°-30°	763.3	28.8
30°-40°	736.4	27.8
40°-50°	384.0	14.5
50°-60°	80.8	3.1
60°-70°	18.8	0.7
70°-80°	7.3	0.3
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1419.8	53.6
0°-40°	2156.3	81.4
0°-60°	2621.1	99.0
0°-90°	2647.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2647.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1655	
5°	1669	160
15°	1756	496
25°	1673	763
35°	1195	736
45°	488	384
55°	73	81
65°	17	19
75°	7	7
85°	0	0
90°	0	



TEST NUMBER: P206777

CATALOG NUMBER: LD4B40D010 EU4B30509730 4LBWWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1655.4
2.5°	1658.9
5°	1669.3
7.5°	1683.1
10°	1703.9
12.5°	1731.6
15°	1755.8
17.5°	1769.7
20°	1759.3
22.5°	1738.5
25°	1672.7
27.5°	1593.1
30°	1489.2
32.5°	1350.6
35°	1194.8
37.5°	1025.1
40°	848.5
42.5°	671.9
45°	488.3
47.5°	329.0
50°	211.3
52.5°	128.1
55°	72.7
57.5°	45.0
60°	31.2
62.5°	24.2
65°	17.3
67.5°	13.9
70°	10.4
72.5°	10.4
75°	6.9
77.5°	3.5
80°	3.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)