

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206235

Luminaire Tested: **LD4B20D010 EU4B10209730 4LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206235
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10209730 4LBPSMW1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1611.8 lumens
Efficiency: N/A
Efficacy: 77.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206235

CATALOG NUMBER: LD4B20D010 EU4B10209730 4LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P206235

CATALOG NUMBER: LD4B20D010 EU4B10209730 4LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63			
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206235

CATALOG NUMBER: LD4B20D010 EU4B10209730 4LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.5	3.8
10°-20°	175.4	10.9
20°-30°	264.1	16.4
30°-40°	314.3	19.5
40°-50°	313.7	19.5
50°-60°	255.1	15.8
60°-70°	157.0	9.7
70°-80°	60.8	3.8
80°-90°	9.7	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	501.1	31.1
0°-40°	815.4	50.6
0°-60°	1384.3	85.9
0°-90°	1611.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1611.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	649	
5°	648	62
15°	623	175
25°	575	264
35°	503	314
45°	408	314
55°	286	255
65°	158	157
75°	55	61
85°	8	10
90°	0	



TEST NUMBER: P206235

CATALOG NUMBER: LD4B20D010 EU4B10209730 4LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	649.4
2.5°	650.3
5°	647.5
7.5°	643.7
10°	638.9
12.5°	630.3
15°	622.7
17.5°	611.2
20°	598.8
22.5°	587.3
25°	574.9
27.5°	557.7
30°	540.5
32.5°	524.3
35°	503.3
37.5°	480.4
40°	459.3
42.5°	433.6
45°	407.8
47.5°	380.1
50°	350.5
52.5°	319.9
55°	285.5
57.5°	252.1
60°	219.6
62.5°	188.1
65°	157.6
67.5°	128.9
70°	102.2
72.5°	77.4
75°	55.4
77.5°	36.3
80°	22.0
82.5°	13.4
85°	7.6
87.5°	3.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)