

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P252080

Luminaire Tested: **LD4B20D010 EU4B10208050 4LBBA1MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P252080
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-4)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10208050 4LBBA1MB
Description: PORTFOLIO 4 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE BLACK TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1048.0 lumens
Efficiency: N/A
Efficacy: 50.4 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 0.94
Luminous Opening: Circular (Dia: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P252080

CATALOG NUMBER: LD4B20D010 EU4B10208050 4LBBA1MB

Luminous Intensity Polar Plot





TEST NUMBER: P252080

CATALOG NUMBER: LD4B20D010 EU4B10208050 4LBBA1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	88	83	79	86	82	78	84	81	77	82	79	77	75			
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65			
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61			
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	61	58	57			
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53			
10	72	62	56	52	71	61	56	52	60	55	52	60	55	52	59	55	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	102146
5°	101871
10°	100881
15°	99262
20°	96359
25°	89016
30°	72214
35°	44770
40°	21068
45°	7360
50°	2077
55°	1393
60°	1072
65°	945
70°	769
75°	527
80°	786
85°	0



TEST NUMBER: P252080

CATALOG NUMBER: LD4B20D010 EU4B10208050 4LBBA1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.7	9.4
10°-20°	276.5	26.4
20°-30°	371.7	35.5
30°-40°	237.5	22.7
40°-50°	50.5	4.8
50°-60°	7.6	0.7
60°-70°	3.7	0.4
70°-80°	1.6	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	746.9	71.3
0°-40°	984.4	93.9
0°-60°	1042.5	99.5
0°-90°	1048.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1048.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1048	
5°	1041	99
15°	984	277
25°	828	372
35°	376	237
45°	53	51
55°	8	8
65°	4	4
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P252080

CATALOG NUMBER: LD4B20D010 EU4B10208050 4LBBA1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1048.1
2.5°	1046.7
5°	1041.3
7.5°	1031.7
10°	1019.4
12.5°	1003.0
15°	983.8
17.5°	959.2
20°	929.1
22.5°	886.7
25°	827.8
27.5°	745.7
30°	641.7
32.5°	513.1
35°	376.3
37.5°	257.2
40°	165.6
42.5°	98.5
45°	53.4
47.5°	27.4
50°	13.7
52.5°	9.6
55°	8.2
57.5°	6.8
60°	5.5
62.5°	4.1
65°	4.1
67.5°	2.7
70°	2.7
72.5°	1.4
75°	1.4
77.5°	1.4
80°	1.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)