

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207385

Luminaire Tested: **LD4B40D010 EU4B30508035 4LBMGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207385
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30508035 4LBMGPH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2261.5 lumens
Efficiency: N/A
Efficacy: 54.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.92
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207385

CATALOG NUMBER: LD4B40D010 EU4B30508035 4LBMGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P207385

CATALOG NUMBER: LD4B40D010 EU4B30508035 4LBMGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	88	86			
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79			
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73			
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68			
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63			
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59			
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55			
9	73	63	57	53	72	63	57	53	62	57	53	61	56	53	60	56	52	51			
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	52	49	48			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207385

CATALOG NUMBER: LD4B40D010 EU4B30508035 4LBMGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	213.9	9.5
10°-20°	557.9	24.7
20°-30°	715.6	31.6
30°-40°	517.2	22.9
40°-50°	185.4	8.2
50°-60°	50.0	2.2
60°-70°	16.4	0.7
70°-80°	5.0	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1487.4	65.8
0°-40°	2004.6	88.6
0°-60°	2240.1	99.1
0°-90°	2261.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2261.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2325	
5°	2282	214
15°	1987	558
25°	1578	716
35°	827	517
45°	224	185
55°	52	50
65°	14	16
75°	5	5
85°	0	0
90°	0	



TEST NUMBER: P207385

CATALOG NUMBER: LD4B40D010 EU4B30508035 4LBMGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2325.0
2.5°	2315.5
5°	2282.2
7.5°	2229.9
10°	2158.6
12.5°	2077.7
15°	1987.4
17.5°	1897.1
20°	1806.7
22.5°	1702.1
25°	1578.5
27.5°	1435.9
30°	1255.2
32.5°	1046.0
35°	827.3
37.5°	627.6
40°	456.4
42.5°	323.3
45°	223.5
47.5°	152.1
50°	99.8
52.5°	71.3
55°	52.3
57.5°	38.0
60°	28.5
62.5°	23.8
65°	14.3
67.5°	9.5
70°	9.5
72.5°	4.8
75°	4.8
77.5°	4.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)