

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207052

Luminaire Tested: **LD4B20D010 EU4B10208050 4LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207052
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10208050 4LBWMW1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1831.3 lumens
Efficiency: N/A
Efficacy: 88.0 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207052

CATALOG NUMBER: LD4B20D010 EU4B10208050 4LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P207052

CATALOG NUMBER: LD4B20D010 EU4B10208050 4LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78			
3	96	87	80	75	93	85	79	74	83	77	73	80	76	72	78	74	71	69			
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61			
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55			
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	60	55	51	50			
7	73	61	53	48	71	60	53	48	59	52	47	57	51	47	56	51	47	45			
8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41			
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38			
10	61	49	42	37	59	48	41	37	47	41	37	46	41	37	46	40	36	35			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207052

CATALOG NUMBER: LD4B20D010 EU4B10208050 4LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.2	5.7
10°-20°	291.4	15.9
20°-30°	411.8	22.5
30°-40°	398.9	21.8
40°-50°	269.1	14.7
50°-60°	167.1	9.1
60°-70°	111.6	6.1
70°-80°	61.1	3.3
80°-90°	16.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	807.3	44.1
0°-40°	1206.2	65.9
0°-60°	1642.4	89.7
0°-90°	1831.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1831.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1110	
5°	1100	104
15°	1034	291
25°	903	412
35°	642	399
45°	345	269
55°	183	167
65°	112	112
75°	57	61
85°	14	16
90°	0	



TEST NUMBER: P207052

CATALOG NUMBER: LD4B20D010 EU4B10208050 4LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1109.7
2.5°	1109.7
5°	1100.2
7.5°	1088.3
10°	1074.1
12.5°	1059.8
15°	1033.7
17.5°	1012.3
20°	976.6
22.5°	941.0
25°	903.0
27.5°	850.7
30°	793.7
32.5°	720.0
35°	641.6
37.5°	563.2
40°	484.7
42.5°	406.3
45°	344.6
47.5°	287.5
50°	244.8
52.5°	209.1
55°	183.0
57.5°	161.6
60°	144.9
62.5°	128.3
65°	111.7
67.5°	97.4
70°	83.2
72.5°	71.3
75°	57.0
77.5°	45.1
80°	33.3
82.5°	23.8
85°	14.3
87.5°	4.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)